



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Ribbon Cable Connector: Pull Loop



Flat Flexible Cable Accessory Type: Pull Loop

[All Ribbon Cable Connector: Pull Loop \(10\)](#)

Features

Product Type Features

Flat Flexible Cable Accessory Type	Pull Loop
------------------------------------	-----------

Body Features

Primary Product Material	PVC
Primary Product Color	Natural

Dimensions

	2.8 in
--	--------

Industry Standards

CSA File Number	LR 7189
Agency/Standard	CSA, UL
UL Rating	Recognized
UL File Number	E28476

Packaging Features

Packaging Quantity	250
Packaging Method	Box & Carton

Other



Comment	60 Posn Conn
---------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 499252-7
060 STRAIN RELIEF A-L RCPT

TE Part # 1-1658622-0
50 NOVO MIL/CTR 30DP,LEAD FREE

TE Part # 1-1658621-0
50 NOVO MIL/CTR 15DP,LEAD FREE

Documents

Product Drawings
PULL LOOP, CUT LENGTH 2.80 IN



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-5088450-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-5088450-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-5088450-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English