




TE Internal #: 2007099-1  
 SFP, SFP+ & zSFP+, Accessory, Data Rate (Max) 16 Gb/s, SFP+,  
 With Lightpipe, 1 x 4, Dual Round, Reduced Length, Standard, 4  
 Port

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP, SFP+ & zSFP+



Pluggable I/O Product Type: **Accessory**

Data Rate (Max): **16 Gb/s**

Pluggable I/O Applications: **SFP+**

Lightpipe Options: **With Lightpipe**

Port Matrix Configuration: **1 x 4**

## Features

### Product Type Features

Form Factor	SFP+
Pluggable I/O Accessory Type	Lightpipe Kit
Cage Type	Ganged
Pluggable I/O Product Type	Accessory
Lightpipe Options	With Lightpipe
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Port Matrix Configuration	1 x 4
Lightpipe Configuration	Dual Round
Lightpipe Style	Reduced Length
Lightpipe Profile	Standard
Number of Ports	4

### Electrical Characteristics

--	--



Data Rate (Max)	16 Gb/s
-----------------	---------

### Operation/Application

Heat Sink Compatible	No
For Use With Pluggable I/O Products	SFP+ Cage
Pluggable I/O Applications	SFP+
Circuit Application	Signal

### Packaging Features

Packaging Method	Box
------------------	-----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CAT-SF59-C117ST123  
SFP+ Stacked Cage Assemblies



TE Part # CAT-C11-H50626  
SFP+ to SFP+ I/O Cable Assembly: 30 AWG



TE Part # 2007135-1  
SFP+ 1x4 CageAssembly w/ EMI gasket



TE Part # 2007132-1  
SFP+ 1X4 Cage Assembly, Press-gasket



TE Part # 2149730-3  
SFP+ Enhanced 1x4 Cage, SAN Heatsink



TE Part # 2149730-4  
SFP+ Enhanced 1x4 Cage, Network Heatsink



TE Part # 2057162-1  
SFP+ 1X4 Cage Assembly, PF, EF



TE Part # 2169260-1  
SFP+ 1x4 Cage Assy, Extended H



TE Part # 2057353-1  
SFP+ Enhanced 1x4 Cage Assy



TE Part # 2057833-1  
SFP+ Enhanced 1x4 Cage Assy



TE Part # 2198241-3  
SFP+ Enhanced 1x4, Networking Heatsink



TE Part # 2198241-4  
SFP+ Enhanced 1x4, Networking Heatsink



TE Part # CAT-C11-H5  
SFP+ to SFP+ I/O Cable Assembly: 24 AWG



TE Part # CAT-C11-H506  
SFP+ to SFP+ I/O Cable Assembly: 26 AWG



TE Part # CAT-C11-H5062  
SFP+ to SFP+ I/O Cable Assembly: 28 AWG



TE Part # 2057161-1  
SFP+ Enhanced 1x4 Cage Assy



TE Part # 2142970-1  
CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M



TE Part # 2142970-2  
CABLE ASSY, MICRO SFP+ TO STD SFP+, 1M



TE Part # 2142970-3  
CABLE ASSY, MICRO SFP+ TO STD SFP+, 2M



TE Part # 2142970-4  
CABLE ASSY, MICRO SFP+ TO STD SFP+, 3M

## Documents

[Product Drawings](#)  
[SFP+ 1x4 Light Pipe Assembly](#)



English

---

**CAD Files**

Customer View Model

[ENG\\_CVM\\_CVM\\_2007099-1\\_A.2d\\_dxf.zip](#)

English

**3D PDF**

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2007099-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2007099-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Specifications**

[Product Specification](#)

English

---

**Product Environmental Compliance**

[TE Material Declaration](#)

English