



Connectors > Pluggable IO Connectors & Cages > QSFP, QSFP+ & zQSPF+



Pluggable I/O Product Type: **Accessory**

Lightpipe Configuration: **Dual Round**

### Features

#### Product Type Features

Form Factor	QSFP+
Pluggable I/O Accessory Type	Lightpipe
Pluggable I/O Product Type	Accessory

#### Configuration Features

Lightpipe Configuration	Dual Round
-------------------------	------------

#### Operation/Application

For Use With Pluggable I/O Products	QSFP+ Cage
-------------------------------------	------------

#### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

#### Packaging Features

Packaging Method	Box & Tray
------------------	------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-C11-H501114  
QSFP to QSFP I/O Cable Assembly: 30 AWG



TE Part # CAT-C11-H50111  
QSFP-Four SFP+ I/O Cable Assembly 30 AWG



TE Part # 2110819-1  
QSFP+ Enh EVERCLEAR PT Conn



TE Part # 2007668-1  
1x4 QSFP Cage Assy Behind Bzl, LP Holder



TE Part # 1888810-2  
EMI/Dust Cover,XFP And QSFP



TE Part # 2007473-1  
1x3 QSFP Cage Assy Behind Bzl



TE Part # CAT-C11-H5011  
QSFP-Four SFP+ I/O Cable Assembly 28 AWG



TE Part # CAT-C11-H5011142  
QSFP to QSFP I/O Cable Assembly: 33 AWG



TE Part # 2053638-5  
C/A, QSFP, 5M, P1-P2, UNEQUALIZED



TE Part # 1-2220639-0  
QSFP TO QSFP, ACTIVE, 28AWG, 10M



TE Part # 1-2220639-3  
QSFP TO QSFP, ACTIVE, 28AWG, 13M



TE Part # 2053638-4  
C/A, QSFP, 4M, P1-P2, UNEQUALIZED



TE Part # 2202165-4  
QSFP TO QSFP, 26AWG, FDR, 4.0  
METER



TE Part # 2202165-5  
QSFP TO QSFP, 26AWG, FDR, 5.0  
METER



TE Part # 2829040-2  
QSFP IB EDR, 33AWG, 1.0M



TE Part # 2829040-4  
QSFP IB EDR, 30AWG, 1.0M



TE Part # 2829040-6  
QSFP IB EDR, 30AWG, 2.0M



TE Part # 2829040-7  
QSFP IB EDR, 26AWG, 2.0M



TE Part # 2829040-8  
QSFP IB EDR, 26AWG, 3.0M



TE Part # 2821033-8  
QSFP TO [4]SFP+, 28G, 1M, 33AWG

Also in the Series | **QSFP/QSFP+**



Heat Sinks(1)



Pluggable I/O Cable Assemblies(33)



QSFP, QSFP+ & zQSFP+(168)

Documents

Product Drawings

1xN QSFP Bhnd Bzl Dbl L Pipe

English

CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2007477-3\\_B\\_c-2007477-3-b.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2007477-3\\_B\\_c-2007477-3-b.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2007477-3\\_B\\_c-2007477-3-b.3d\\_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

[1773408-1 Pluggable Input/Output Solutions catalog - QSFP section](#)

English

[4-1773455-5 - Quick Reference Guide QSFP/QSFP+ Solutions](#)

English