

213920-2 ✓ ACTIVE

AMP | AMP CPC


TE Internal #: 213920-2

Circular Connector Seals, Wire Entry Seal Kit, 16 Position, 15/16-20, -67 – 221 °F [-55 – 105 °C], AMP CPC

[View on TE.com >](#)



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Seals > CPC SERIES 5 SEALED ACCESSORIES



Connector Seal Type: **Wire Entry Seal Kit**

Number of Positions: **16**

Screw & Hole Thread Size: **15/16-20**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

[All CPC SERIES 5 SEALED ACCESSORIES \(6\)](#)

## Features

### Product Type Features

Connector Seal Type	Wire Entry Seal Kit
---------------------	---------------------

### Configuration Features

Number of Positions	16
---------------------	----

### Mechanical Attachment

Screw & Hole Thread Size	15/16-20
--------------------------	----------

### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Packaging Features

Packaging Quantity	1
--------------------	---

Packaging Method	Individual
------------------	------------

### Other

Comment	Kit for Pins, Kit includes (1) Gang Seal and (1) Pressure Plate marked for cavity identification.
---------	---

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # CAT-AM71-C83998U  
Environmentally Sealed Circular Connector, CPC Series 5

TE Part # CAT-AM71-C83998K  
Circular Connector, Environmentally Sealed, CPC Series 6

TE Part # 213906-1  
CPC PLUG ASSY,SRS 6,SZ 17-10

TE Part # 213899-1  
CPC SEAL ASSY KIT,SRS 5,17-3

TE Part # 213900-1  
CPC SEAL ASSY KIT,SRS 6,17-10

TE Part # 197889-1  
ANVIL HOLDER

Also in the Series | **AMP CPC**



Circular Connector Adapters(7)



Circular Connector Boots &amp; Strain Relief(6)



Circular Connector Caps &amp; Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Connector Seals(36)



Circular Power Connectors(467)



Insertion &amp; Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells &amp; Clamps(56)

## Documents

### Product Drawings

CPC SEAL KIT,UNASSM,SZ 17-16

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_213920-2\\_D.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_213920-2\\_D.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_213920-2\\_D.3d\\_stp.zip](#)

English

3D PDF

English



**Customer View Model**

[ENG\\_CVM\\_213920-2\\_C.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_213920-2\\_C.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_213920-2\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

---

**Product Specifications**

[Product Specification](#)

English

---

**Instruction Sheets**

[Instruction Sheet \(U.S.\)](#)

English