

2142970-7 ✓ ACTIVE

microSFP+

TE Internal #: 2142970-7

Pluggable I/O Cable Assemblies, Micro SFP+ to SFP+, 26 AWG

Wire Size, .129 mm² Wire Size, .235 in [5.96 mm] Diameter,

Shielded, microSFP+

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Cable Assembly Type: **Micro SFP+ to SFP+**

Equalized: **No**

Wire Size: **.129 mm²**

Outside Cable Diameter: **5.96 mm [.235 in]**

Features

Product Type Features

Cable Assembly Category	High Speed
Cable Assembly Type	Micro SFP+ to SFP+
Connector Type (End A)	Micro SFP+ Plug
Connector Type (End B)	SFP+ Plug
Cable Style	Madison TurboTwin - Round Jacketed

Configuration Features

Number of Positions	4
Number of Pairs	2
Number of Signal Positions	4

Electrical Characteristics

Impedance	100 Ω
-----------	-------

Signal Characteristics

Data Rate	10 Gb/s
-----------	---------

Body Features

Equalized	No
Cable Color	Black
Cable Flammability Rating	UL 1581

Dimensions

--	--



Wire Size	.129 mm ²
Outside Cable Diameter	5.96 mm [.235 in]

Operation/Application

Shielded	Yes
Halogen Free	Yes

Other

Cable Assembly Length	6 m [6 ft]
-----------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2013 (144) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-SF59-C117ST123
SFP+ Stacked Cage Assemblies



TE Part # CAT-SF59-C76264
SFP Connectors



TE Part # CAT-SF59-AC229
SFP accessories



TE Part # 2007250-1
SFP+ 1x6 Cage Assembly with Light Pipes



TE Part # 2007135-1
SFP+ 1x4 Cage Assembly w/ EMI gasket



TE Part # 2007254-1
SFP+ 1x1 Cage Assembly, Light Pipe



TE Part # 2198230-2
SFP+ Enhanced 1x2, SAN Heatsink



TE Part # 2198230-1
SFP+ Enhanced 1x2, PCI Heatsink



TE Part # 2170030-1
SFP+ 1x4 w/ Ultra Low Profile LP



TE Part # 2007194-2
SFP+ 1x1 Cage Assembly, PCI, Solder Tail



TE Part # 2007181-1
SFP+ 1x2 Cage Assy, EMI Gasket



TE Part # 2007194-1
SFP+ 1x1 Cage Assembly, PCI, Solder Tail



TE Part # 2110304-1
SFP+ 1x1 Cage Assembly, Solder Tail



TE Part # 2007251-1
SFP+ 1x6 Cage Assembly



TE Part # 2007178-1
SFP+ 1x4 Cage Assembly, Light



TE Part # 2007262-1
SFP+ 1x2 Cage Assembly, Light



TE Part # 2198235-3
SFP+ Enhanced 1x6, Networking Heatsink



TE Part # 2198230-3
SFP+ Enhanced 1x2, Networking Heatsink



TE Part # 2007263-1
SFP+ 1x2 Cage Assembly



TE Part # 2007464-3
SFP+ 1x1 Cage Assy, PF, with Heatsink

Also in the Series | **microSFP+**



Pluggable I/O Cable Assemblies(7)



SFP, SFP+ & zSFP+(1)

Documents

Datasheets & Catalog Pages

[MICRO SFP+ CONNECTOR & CABLE ASSEMBLY](#)

English

Product Specifications

[Application Specification](#)

English