




Connectors > Lighting Connectors > Street Lighting Controls > ANSI Street Lighting Receptacles



Lighting Product Type: **Gasket**

Features

Product Type Features

Lighting Product Type	Gasket
-----------------------	--------

Housing Features

Housing Color	Black
---------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-ST833-R2435A
DIMMING RECEPTACLE



TE Part # CAT-ST833-L97
Receptacle Assembly



TE Part # 1-2314670-4
RCPT ASSY,DIMMABLE
PHOTOCONTROL,105C,3/4



TE Part # 2314670-3
Rcpt Assy,Dimmable Photocontrol,
105C,3/2



TE Part # 2314670-4
RCPT ASSY,DIMMABLE
PHOTOCONTROL,105C,3/4

Also in the Series | LUMAWISE Endurance N



ANSI Street Lighting Accessories(17)



ANSI Street Lighting Base Assemblies
(13)



ANSI Street Lighting Receptacles(25)



Street Lighting Open & Shorting Caps
(3)



Street Lighting Power Management(6)



Documents

Product Drawings

[GASKET, PHOTOCCELL RECEPTACLE](#)

English

Datasheets & Catalog Pages

[LUMAWISE STREET LIGHT DIMMING AND CONTROL QUICK REFERENCE GUIDE](#)

English

[LUMAWISE DIMMING RECEPTACLE universal MATE-N-LOK Connectors](#)

[LUMAWISE DIMMING RECEPTACLE universal MATE-N-LOK Connectors](#)

English

[LUMAWISE DIMMING RECEPTACLE IEC 61984 - Double Insulation](#)

[LUMAWISE DIMMING RECEPTACLE IEC 61984 - Double Insulation](#)

English

[LUMAWISE Endurance N ANSI C136.41 Standard Dimming Receptacle Assembly](#)

English

Product Specifications

[Application Specification](#)

English