

27E213 ✓ ACTIVE

Potter & Brumfield | Potter & Brumfield R10


TE Internal #: 2-1393143-5

Relay Accessories, Sockets & Clips, Socket, Printed Circuit Board, Polyester, R10 Relays, Printed Circuit Board, 4, Socket, Potter & Brumfield R10

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Relay Accessories, Sockets & Clips



Relay Accessory, Socket & Clip Product Type: **Socket**

Relay Accessory, Socket & Clip Socket Type: **Printed Circuit Board**

Grounding Provision: **Without**

Relay Accessory, Socket & Clip Body Material: **Polyester**

Relay Accessory, Socket & Clip For Use With: **R10 Relays**

Features

Product Type Features

Terminal Configuration	PC Stag
Relay Accessory, Socket & Clip Product Type	Socket
Relay Accessory Type	Socket

Configuration Features

Grounding Provision	Without
---------------------	---------

Body Features

Relay Accessory, Socket & Clip Body Material	Polyester
--	-----------

Contact Features

Terminal Length	4.57 mm[.18 in]
Contact Plating Material	Tin
Contact Base Material	Spring Brass
Relay Accessory, Socket & Clip Socket Type	Printed Circuit Board
Pole Configuration	4

Termination Features

Number of Pins	16
----------------	----

Mechanical Attachment

Relay Accessory, Socket & Clip Mounting Type	Printed Circuit Board
--	-----------------------

Operation/Application

Relay Accessory, Socket & Clip For Use With

R10 Relays

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 8-1393766-0
R10-E1Z4-V2.5K=R10



TE Part # 3-1393159-6
20C250=SPRING,HOLD-DOWN,R10,.0



TE Part # 9-1393765-5
R10-E1W4-V700=R10



TE Part # 1-1393766-7
R10-E1X4-V700=R10




TE Part # 5-1393766-3
R10-E1Y4-V185=R10



TE Part # 5-1393766-5
R10-E1Y4-V2.5K=R10



TE Part # 4-1393159-5
20C301=SPRING



TE Part # 1-1393766-3
R10-E1X4-V15.0K=R10



TE Part # 8-1393766-1
R10-E1Z4-V700=R10



TE Part # 5-1393766-7
R10-E1Y4-V700=R10



TE Part # 7-1393765-4
R10-E1P4-V185=R10



TE Part # 9-1393765-3
R10-E1W4-V185=R10



TE Part # 8-1419135-6
R10-E1X4-V52=R10



TE Part # 5-1393766-6
R10-E1Y4-V52=R10



TE Part # 7-1393766-6
R10-E1Z4-J1.0K=R10



TE Part # 7-1393769-7
R10S-E1Y4-J1.0K=R10



TE Part # 1-1393766-5
R10-E1X4-V2.5K=R10



TE Part # 4-1393766-8
R10-E1Y4-J1.0K=R10




TE Part # 4-1393766-6
R10-E1Y4-JJ1.0K=R10




TE Part # 4-1393766-7
R10-E1Y4-JJ2.5K=R10

Also in the Series | **Potter & Brumfield R10**



PCB Headers & Receptacles(1)



Power Relays(180)



Relay Accessories, Sockets & Clips(30)

Documents



CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-1393143-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1393143-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1393143-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

R10 Sockets & Accessories

English

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English

Product Environmental Compliance

TE Material Declaration

English