

2-175133-2 ✓ ACTIVE

## AMP CT

TE Internal #: 2-175133-2

PCB Connector Mounting, Holder, Wire-to-Board, 22 Position, .079 in [2 mm] Centerline, 28 – 24 AWG Wire Size, Ivory, AMP CT

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > Mounting



Connector Mounting Accessory Type: **Holder**

Connector System: **Wire-to-Board**

Number of Positions: **22**

Centerline (Pitch): **2 mm [ .079 in ]**

Wire Size: **28 – 24 AWG**

### Features

#### Product Type Features

Connector Mounting Accessory Type	Holder
Connector System	Wire-to-Board

#### Configuration Features

Number of Positions	22
---------------------	----

#### Body Features

Primary Product Material	PA 66
Primary Product Color	Ivory

#### Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

#### Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

#### Dimensions

Product Width	7.55 mm[.297 in]
Product Length	26.3 mm[1.035 in]
Product Height	6.65 mm[.261 in]
Row-to-Row Spacing	6.6 mm
Wire Size	28 – 24 AWG

#### Usage Conditions



Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

### Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

### Other

Comment	For Use With CT Connector, Two receptacle connectors are applied per holder.
---------	--

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CAT-AM7017-C7671  
AMP COMMON TERMINATION  
CONTACTS



TE Part # CAT-3980700-DRWBSV  
CT 2mm Dbl Row Assembly w/Boss:  
Vert.



TE Part # CAT-AM7017-H8172  
AMP COMMON TERMINATION  
HOUSINGS



TE Part # 353918-1  
CT 1.5MM REC CONT CRIMP TYPE



TE Part # 2-292138-2  
CT DOUBLE ROW ASSY H 22P HDR N



TE Part # 2-84580-2  
2MM CT D/R HDR ASSY H/TEMP 22P


## Also in the Series | AMP CT




PCB Connector Mounting(46)



PCB Headers & Receptacles(756)



Wire-to-Board Connector Assemblies  
& Housings(256)



Wire-to-Board Connector Contacts(8)

## Documents

### Product Drawings

CT DOUBLE ROW 22P HOLDER NATU.

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-175133-2\\_E.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-175133-2\\_E.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-175133-2\\_E.3d\\_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

[2.0MM\\_AMP\\_CT\\_CONNECTOR\\_SERIES\\_QUICK\\_REF\\_GUIDE](#)

English

---

## Product Specifications

[Application Specification](#)

English

[Crimping of AMP 2.0mm Pitch, CT Crimp Typell Rec Contact](#)

English

[Application Specification](#)

English

---

## Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

---

## Agency Approvals

[CSA Certificate](#)

English