

2-2205130-3 ✓ ACTIVE



TE Internal #: 2-2205130-3

Pluggable I/O Cable Assemblies, INDUSTRIAL MINI I/O Pigtail, 26

AWG Wire Size, .129 mm<sup>2</sup> Wire Size, .244 in [6.2 mm] Diameter,

Shielded

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Cable Assembly Type: INDUSTRIAL MINI I/O Pigtail

Equalized: No

Wire Size: .129 mm<sup>2</sup>

Outside Cable Diameter: 6.2 mm [ .244 in ]

## Features

### Product Type Features

Latching Style	Slide Latch
Twisted Pairs	Yes
Performance Category	Category 5E Performance for 10/100 /1000BASE-T
Product Type	Cable Assembly
Product Designation	Patch Cord
Cable Assembly Category	Industry Standard
Cable Assembly Type	INDUSTRIAL MINI I/O Pigtail
Connector Type (End A)	INDUSTRIAL MINI I/O Plug

### Configuration Features

Configuration	Single-Ended
Number of Positions	8
Number of Signal Positions	8

### Electrical Characteristics

Impedance	100 Ω
-----------	-------

### Signal Characteristics

Data Rate	1 Gb/s
-----------	--------

### Body Features

Shield Material	Copper Alloy
-----------------	--------------



Jacket Material	PUR
-----------------	-----

Equalized	No
-----------	----

Cable Color	Black
-------------	-------

Cable Flammability Rating	UL 444
---------------------------	--------

### Contact Features

Contact Mating Area Plating Thickness	.5 μm, 19.68 μin
---------------------------------------	------------------

Contact Mating Area Plating Material	Gold
--------------------------------------	------

### Mechanical Attachment

Jackscrew	Without
-----------	---------

### Housing Features

Housing Material	Thermoplastic
------------------	---------------

### Dimensions

Wire Size	.129 mm <sup>2</sup>
-----------	----------------------

Outside Cable Diameter	6.2 mm [.244 in]
------------------------	------------------

### Operation/Application

Shielded	Yes
----------	-----

Halogen Free	Yes
--------------	-----

### Industry Standards

IEEE 1394	No
-----------	----

### Other

CLOUDSPLITTER	No
---------------	----

Cable Assembly Length	2 m [6.56 ft]
-----------------------	---------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
--	--

Halogen Content

Not Low Halogen - contains Br or Cl &gt; 900 ppm.

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

## Product Drawings

CA MINI IO TYPE II PIGTAIL

English

## Product Specifications

Application Specification

English

## Product Environmental Compliance

Product Compliance

English

Product Compliance

English