

499252-5 ✓ ACTIVE

AMP-LATCH

TE Internal #: 499252-5

TE Internal Description: 010 STRAIN RELIEF A-L RCPT


Bus Connector: Strain Relief, ATA

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Bus Connector: Strain Relief, ATA



Flat Flexible Cable Accessory Type: **Strain Relief**

[All Bus Connector: Strain Relief, ATA \(13\)](#)

Features

Product Type Features

| | |
|------------------------------------|---------------|
| Flat Flexible Cable Accessory Type | Strain Relief |
|------------------------------------|---------------|

Body Features

| | |
|--------------------------|---------------|
| Primary Product Material | Thermoplastic |
|--------------------------|---------------|

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Dimensions

| | |
|---------------|----------------|
| Product Width | 6.1 mm[.24 in] |
|---------------|----------------|

| | |
|----------------|------------------|
| Product Length | 17.53 mm[.69 in] |
|----------------|------------------|

| | |
|----------------|-------------------|
| Product Height | 14.76 mm[.581 in] |
|----------------|-------------------|

Industry Standards

| | |
|-----------------|---------|
| CSA File Number | LR 7189 |
|-----------------|---------|

| | |
|-----------------|---------|
| Agency/Standard | CSA, UL |
|-----------------|---------|

| | |
|-----------|------------|
| UL Rating | Recognized |
|-----------|------------|

| | |
|----------------|--------|
| UL File Number | E28476 |
|----------------|--------|

Packaging Features

| | |
|--------------------|-----|
| Packaging Quantity | 500 |
|--------------------|-----|



Packaging Method

Bag & Box

Other

Comment

Receptacle Connector

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS




TE Part # 1-111446-4
10 UNIV I/O, NO EARS, LEAD FREE



TE Part # 1-111504-4
10 UNIV I/O, NO EARS, LEAD FREE



TE Part # 2-1761605-3
IDC LOW PRO HDR 10P RA BLUE



TE Part # 1761681-3
IDC LOW PRO HDR 10P VERT HT
BLACK



TE Part # 1658621-1
10 NOVO MIL/CTR 15DP, LEAD FREE



TE Part # 2-1761603-3
IDC LOW PRO HDR 10P VERT BLUE



TE Part # 1761607-3
IDC LOW PRO HDR 10P RA LG LAT



TE Part # 5104338-1
A/L LOW PRO HDR 10P VERT HT



TE Part # 5103311-1
A/L LOW PRO HDR 10P RA BLACK



TE Part # 1-111506-6
010 UNIV I/O 30DP SLOT LTCH



TE Part # 1761606-3
IDC LOW PRO HDR 10P VERT LG LAT
BLK



TE Part # 2-1761711-3
IDC LOW PRO HDR 10P VERT LG LA



TE Part # 5103310-1
A/L LOW PRO HDR 10P RA BLACK



TE Part # 5103309-1
A/L LOW PRO HDR 10P VERT BLACK



TE Part # 5103308-1
A/L LOW PRO HDR 10P VERT BLACK



TE Part # 5104340-1
A/L LOW PRO HDR 10P RA HT



TE Part # 2-1761606-3
IDC LOW PRO HDR 10P VERT LG LAT
BLUE



TE Part # 1658620-1
10 NOVO MIL 15DP, LEAD FREE



TE Part # 2-1761607-3
IDC LOW PRO HDR 10P RA LG LAT

Documents

Product Drawings

010 STRAIN RELIEF A-L RCPT

English

CAD Files

Customer View Model

[ENG_CVM_CVM_499252-5_AL.2d_dxf.zip](#)

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_499252-5_AL.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_499252-5_AL.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_499252-5_10052017233_dmtec](#)

English

[MD_499252-5_10052017233_dmtec](#)

English