

4-6437630-7 ✓ ACTIVE

## Alcoswitch

TE Internal #: 4-6437630-7

Rocker Switches, Power, Panel Cutout Size .511 x .62 in [13 x 15.9 mm], Silver, Double Pole - Double Throw Configuration (Pole-Throw), On On, 6 A

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Rocker Switches



Rocker Switch Type: **Power**

Rocker Switch Mounting Type: **Panel**

Indicator/Imprint Legend: **None**

Panel Cutout Size: **13 x 15.9 mm [ .511 x .62 in ]**

Switch Contact Plating Material: **Silver**

## Features

### Product Type Features

Product Type	Switch
Rocker Switch Type	Power
Lamp	Without
Rocker Switch LED	Without
Actuator Type	Top
Actuator Style	Rocker

### Configuration Features

Indicator/Imprint Legend	None
Panel Cutout Size	13 x 15.9 mm [.511 x .62 in]
Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On On

### Electrical Characteristics

Rocker Switch Voltage Rating	125 VAC, 250 VAC
------------------------------	------------------

### Body Features

Body Color	Black
Actuator Color	Red

### Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------



Rocker Switch Contact Current Rating	6 A
--------------------------------------	-----

### Termination Features

Termination Type	Lead Wire - Hooking Type
------------------	--------------------------

### Mechanical Attachment

Mounting Angle	Vertical
----------------	----------

Rocker Switch Mounting Type	Panel
-----------------------------	-------

### Housing Features

Process Sealed	No
----------------	----

### Industry Standards

VDE Tested	No
------------	----

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
------------------------------	------------------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
-----------------	--

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

### Product Drawings

[FLN29RED04=ROCKER ACTION SWITCH](#)

English

### Datasheets & Catalog Pages

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English

[F\\_SERIES\\_SWITCHES\\_QUICK\\_REF\\_GUIDE\\_1-1773458-9](#)

English