

5745584-3 ✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit


TE Internal #: 5745584-3

D-Sub Locking & Mounting, Slide Latch Kit, Screw Length 10.54 mm [.415 in], AMPLIMITE Kit

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Slide Latch Kit**

Screw Length: 10.54 mm [.415 in]

Features

Product Type Features

Product Type	Accessory
Latch Type	Slide Latch
D-Shaped Connector Accessories	Slide Latch Kit

Body Features

Latch Material	Stainless Steel
----------------	-----------------

Mechanical Attachment

Screw Plating Material	Zinc
Screw Material	Steel
Screw Finish	Yellow Chromate
Screw & Hole Thread Size	4-40
Screw Length	10.54 mm [.415 in]

Operation/Application

For Use With	Connectors With Cable Clamp Housings
--------------	--------------------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions



China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(135)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Documents

Product Drawings

UNIV SLIDELATCH KIT, SZ 3

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_5745584-3_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_5745584-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5745584-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

5745584-3

D-Sub Locking & Mounting, Slide Latch Kit, Screw Length 10.54 mm [.415 in],
AMPLIMITE Kit

