

5747242-1 ✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit

TE Internal #: 5747242-1


D-Sub Locking & Mounting, Sliding Lock Post Kit, Screw Length

5.58 mm [.22 in], AMPLIMITE Kit

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Sliding Lock Post Kit**

Screw Length: **5.58 mm [.22 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Sliding Lock Post Kit

Mechanical Attachment

Locking Post Plating Material	Zinc
Locking Post Finish	Yellow Chromate
Locking Post Material	Cold Rolled Steel
Screw & Hole Thread Size	2-56
Screw Length	5.58 mm [.22 in]

Operation/Application

For Use With	Cable Clamps With Mounting Flanges
--------------	------------------------------------

Packaging Features

Packaging Quantity	2
Packaging Method	Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)



Candidate List Declared Against: JUNE 2022 (224)
 SVHC > Threshold:
 Pb (.35% in Component Part)

Article Safe Usage Statements:
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMPLIMITE Kit



D-Sub Backshells & Clamps(135)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Documents



Product Drawings

AMPLI SLIDING LOCK POST KIT

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5747242-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5747242-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5747242-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

[MD_5747242-1_08092017638_dmtec](#)

English

[MD_5747242-1_08092017638_dmtec](#)

English

Instruction Sheets

Instruction Sheet (U.S.)

English