



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 5-104652-1
10 50/50 GRID DRST SFMNT RCPT




TE Part # 5-104893-1
10 50/50 GRID CABLE RECPT LF




TE Part # 5-147384-1
10 50/50 GRID SMT RCPT VC LF



TE Part # 5-147413-1
10 50/50 GRID RCPT W/O HD SN



TE Part # 5-2267261-1
10 50/50 GRID TH/PiP RCPT VC LF



TE Part # 5-2267254-1
10 50/50 GRID DRST TH RCPT


Also in the Series | **AMPMODU 50/50 Grid**



Insertion & Extraction Tools(1)



PCB Connector Covers(9)



PCB Headers & Receptacles(302)



Ribbon Cable Connectors(34)

Documents

Product Drawings

10 50/50 HDR TH/PiP.320 W/HD SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2267259-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-2267259-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-2267259-1_1.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
AMPMODU 50/50 GRID THRU-HOLE
English

Product Specifications
Application Specification
English

Agency Approvals
UL Report
English