

745205-7 ✓ ACTIVE

AMPLIMITE | AMPLIMITE HDE


TE Internal #: 745205-7

IDC D-Sub Connectors, Receptacle, 26 – 22 AWG Solid Wire Size,
Wire-to-Wire, 15 Position, 2.77 mm [.055 in] Centerline, 2 Row,
AMPLIMITE HDE

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **26 – 22 AWG**

Shielded: **No**

Connector System: **Wire-to-Wire**

Number of Positions: **15**

[All IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm \(10\)](#)

Features

Product Type Features

Grounding Indents	Without
Grade	Standard
Shell Type	All Plastic
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Connector Product Type	Connector Assembly
D-Sub Shell Size	1
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Number of Rows	2
Compatible With Wire & Cable Type	Discrete Wire, Round Jacketed Cable



Body Features

Color	Black
-------	-------

Contact Features

Contact Type	Socket
	30 μin
D-Sub Contact Size	20
Contact Current Rating (Max)	2.4 A

Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	Straight
Mating Connector Lock Type	Mounting Holes
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Enclosure	Without
Centerline (Pitch)	2.77 mm [.055 in]

Dimensions

Solid Wire Size	26 – 22 AWG
Wire Size	.15 – .4 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	112
Packaging Method	Package

Other

Comment	HDE connectors are designed for terminating solid or stranded (7-strand
---------	---



max.) wire.

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-023-DPARS2274
D-Sub Plug Assembly: Standard, Right Angle, Shell Size 2, 2.74mm




TE Part # CAT-AM7-H3
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm

TE Part # CAT-025-DPAVS2274
D-Sub Plug Assembly: Standard, Vertical, Shell Size 2, 2.74mm

TE Part # 745207-7
15 HDE AP PLUG, LEAD FREE



Also in the Series | AMPLIMITE HDE



Documents

Product Drawings

15 HDE AP RECEPT, LEAD FREE

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_745205-7_M1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_745205-7_M1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_745205-7_M1.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English