



Alcoswitch

TE Internal #: 7-1437624-1

Switch Knobs, Knob, Phenolic, Ribbed with Bar Pointer Knob Design, 6.35 mm [.25 in] Shaft Size, 26.2 mm [1.031 in] Diameter, Black, Line

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Phenolic**

Knob Design: **Ribbed with Bar Pointer**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **26.2 mm [1.031 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Ribbed with Bar Pointer

Body Features

Switch Knob Material	Phenolic
Switch Knob Color	Black

Dimensions

Shaft Size	6.35 mm[.25 in]
Switch Knob Diameter	26.2 mm[1.031 in]

Identification Marking

Indicator Style	Line
Indicator Location	Top & Side

Other

Comment	Top spun aluminum inlay
---------	-------------------------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 7-1437624-2 PKGP70B1/4=KNOB PLASTIC W/POIN</p>	 <p>TE Part # 7-1437624-7 PKJ70B1/4=KNOB PLASTIC</p>	 <p>TE Part # 7-1437624-9 PKJT50B1/8=PKJT-50B 1/4</p>	 <p>TE Part # 7-1437624-5 PKJ50B1/8=KNOB PLASTIC</p>
---	---	--	---

Documents

Product Drawings

[PKGP100B1/4=KNOB PLASTIC W/POI](#)

English

Datasheets & Catalog Pages

PKGP100B1/4

Switch Knobs, Knob, Phenolic, Ribbed with Bar Pointer Knob Design, 6.35 mm [.25 in]
Shaft Size, 26.2 mm [1.031 in] Diameter, Black, Line



SWITCHES_CORE_PROGRAM_CATALOG

English