

829261-2 ✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit

TE Internal #: 829261-2

D-Sub Locking & Mounting, Female Screwlocks, Screw Length 12.7 mm [.5 in], AMPLIMITE Kit

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlocks**

Screw Length: 12.7 mm [.5 in]

## Features

### Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlocks

### Mechanical Attachment

Screwlock Style	Screwlock Only
Mating Thread Size	14702
Screw & Hole Thread Size	4-40 UNC 2A (Male), 4-40 UNC 2B (Female)
Screw Length	12.7 mm [.5 in]

### Dimensions

Thread Length	7.9 mm [.311 in]
---------------	------------------

### Packaging Features

Packaging Quantity	2000
Packaging Method	Box

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022  
(224)Candidate List Declared Against: JUNE  
2022 (224)

SVHC &gt; Threshold:

Pb (3.5% in Component Part)

**Article Safe Usage Statements:**Do not eat, drink or smoke when using this product. Wash thoroughly after  
handling. Recycle if possible and dispose of the article by following all applicable  
governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per  
homogenous material. Also BFR/CFR/PVC  
Free


Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(135)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

## Documents

### Product Drawings

[HD.FEMALE SCREWLOCK](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_829261-2\\_J.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_829261-2\\_J.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_829261-2\\_J.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Environmental Compliance

[MD\\_829261-2\\_04102018817\\_dmtec](#)

English

[MD\\_829261-2\\_04102018817\\_dmtec](#)

English