

Item Number 6400000

Dimmable LED Wall Fixture Weathered
Patina Finish Clear Seeded Glass

Specifications

- Height: 12.25"
- Width: 6"
- Extends: 8.00"
- Height from Center of Outlet Box: 2.83"
- Back Plate: H: 5.38" W: 4.38"
- Includes 9 Watt Integrated LED
- Hours: 35000
- Life (years)*: 31.9
- Fixture Lumens: 900
- Color Temperature (Kelvin): 3000
- Equivalent Incandescent Wattage: 60W
- Color Designation: Warm White




Installation

Refer to instruction manual for installation and additional warnings.
Consult a qualified electrician if unsure how to proceed.

Warranty Information - 5 Year Limited Warranty

This Westinghouse Lighting Fixture is warranted against defects in material and workmanship for a period of Five Years from purchase date.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 and Westinghouse are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.