

Item Number 7217800

Halley Ceiling Fan

44 in. Oil Rubbed Bronze Finish
Reversible ABS Blades (Dark Cherry/Mahogany) Frosted Opal Glass

Specifications

Size	44"
Blades.....	Reversible ABS Blades (Dark Cherry/Mahogany)
Blade Pitch.....	13°
Approved Location	Indoor/Outdoor
Suggested Room Size.....	Large Room (up to 15x15)
Down Rod.....	N/A
Installation.....	Hugger
Max. Ceiling Angle.....	N/A
Lead Wire	12"
Light Bulb Usage.....	Includes (2) Medium (E26) Base, 9.8 Watt Omni LED Lamps
Control.....	Remote Control Included
Motor Finish.....	Oil Rubbed Bronze
Motor Material	Silicon Steel Motor 153mm x 17mm
Reverse Airflow.....	Yes
Capacitor	Dual
Switch Housing Cap.....	Not Included



Reversible Mahogany
Finish Blades

Energy Information


	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	N/A	4326
Energy Use (excludes lights) ^A	N/A	35
Airflow (CFM) ^A	N/A	3158
Airflow Efficiency (CFM/W) ^A	N/A	90
Estimated Yearly Energy Cost ^A	N/A	\$10
RPM (High)	260	
Amp (High)	0.43	
Watts (High)	49	



Light Source

Number of Lamps.....	2
Energy Use (Watts) [†]	9.80
Equiv. Incand. Wattage [†]	60
Light Appearance (Kelvin).....	3000
Lumen [†]	800
CRI.....	80
Average Rated Hours.....	25000
Life in Years ^{**†}	22.80
Estimated Yearly Energy Cost..	\$1.18

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

^Δ Based on typical use, excluding lights
^{*} Based on 12 cents per kWh and 6.4 hours use per day
[†] Values are per lamp
^{**} Based on 3hrs./day

Item Number 7217800

Halley Ceiling Fan

44 in. Oil Rubbed Bronze Finish
 Reversible ABS Blades (Dark Cherry/Mahogany) Frosted Opal Glass

A. Top of Canopy to Bottom of Blades	9.5"
B. Top of Canopy to Bottom of Switch House	3"
C. Top of Canopy to Bottom of Canopy	3"
D. Width of Motor Housing.....	9.5"
E. Width of Canopy.....	9.1"
F. Top of Canopy to Bottom of Glass.....	13.8"




If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
 Used under license by Westinghouse Lighting. All Rights Reserved.