

## Item Number 7305500

## Comet Ceiling Fan

52 in. White Finish  
Reversible Blades (Rustic Birch/Graphite) Frosted Glass



### Specifications

Size .....	52"
Blades.....	Reversible Plywood Blades (Rustic Birch/Graphite)
Blade Pitch.....	11°
Approved Location .....	Indoor
Suggested Room Size.....	Great Room (up to 20x20)
Down Rod.....	3/4 x 4"
Installation.....	Combo
Max. Ceiling Angle.....	15°
Lead Wire .....	54"
Light Bulb Usage.....	Includes (2) Candelabra (E12) Base, 5.5 Watt G 16-1/2 LED Lamps
Control.....	Remote control adaptable and pull chain included
Motor Finish.....	White
Motor Material .....	Silicon Steel Motor 153mm x 17mm
Reverse Airflow.....	Yes
Capacitor .....	Triple
Switch Housing Cap.....	Not Included



Reversible Graphite Finish Blades

### Energy Information

	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	4460	3589
Energy Use (excludes lights) <sup>Δ</sup> .....	39	39
Airflow (CFM) <sup>Δ</sup> .....	3210	2492
Airflow Efficiency (CFM/W) <sup>Δ</sup> .....	82	64
Estimated Yearly Energy Cost <sup>Δ</sup> .....	\$11	\$11
RPM (High) .....	147	
Amp (High) .....	0.53	
Watts (High) .....	63	



### Light Source

Number of Lamps.....	2
Energy Use (Watts) <sup>†</sup> .....	5.50
Equiv. Incand. Wattage <sup>†</sup> .....	60
Color Temperature (Kelvin).....	2700
Color Designation: Warm White	
Lumen <sup>†</sup> .....	500
CRI.....	80
Average Rated Hours.....	15000
Life in Years** <sup>†</sup> .....	13.60
Estimated Yearly Energy Cost..	\$0.66

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

<sup>Δ</sup> Based on typical use, excluding lights  
<sup>\*</sup> Based on 12 cents per kWh and 6.4 hours use per day  
<sup>†</sup> Values are per lamp  
<sup>\*\*</sup> Based on 3hrs./day

## Item Number 7305500

## Comet Ceiling Fan

52 in. White Finish  
 Reversible Blades (Rustic Birch/Graphite) Frosted Glass

A. Top of Canopy to Bottom of Blades .....	11.9"
B. Top of Canopy to Bottom of Switch House .....	14.3"
C. Top of Canopy to Bottom of Canopy .....	2.3"
D. Width of Motor Housing.....	11.5"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass.....	14.3"




If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

*Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.*

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.