

Product data sheet

Characteristics

AP7557NA

Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19



Overview

Model Name	<![CDATA[Rack PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19]]>
Includes	Installation guide , Rack Mounting brackets , Toolless Mounting Kit , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Output

Nominal Output Voltage	230V
Maximum Total Current Draw per Phase	16 A
Output Connections	(36) IEC 320 C13 (Battery Backup) , (6) IEC 320 C19 (Battery Backup)
Always on Outlets	0
Overload Protection	No

Input

Nominal Input Voltage	400 3PH
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	16 A
Input Connections	IEC 309 20A 3P+N+E
Cord Length	3 feet (0.91 meters)
Number of Power Cords	0
Maximum Line Current per phase	0 A
Maximum Input Current per phase	20 A
Load Capacity	0 VA

Physical

Net Weight	12.37 lbs (5.62 kg)
------------	---------------------

Maximum Height	70.0 inches (1778.0 mm)
Maximum Width	2.19 inches (56.0 mm)
Maximum Depth	1.73 inches (44.0 mm)
Shipping Weight	20.68 lbs (9.4 kg)
Shipping Height	84.0 inches (2134.0 mm)
Shipping Width	6.0 inches (152.0 mm)
Shipping Depth	5.0 inches (127.0 mm)
Color	Black

Environmental

Operating Environment	23 - 113 °F (-5 - 45 °C)
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 149 °F (-25 - 65 °C)
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	UL 60950-1 , UL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------