



Energetic Lighting's E3-FMA series of LED round flushmount fixtures are designed to emulate the look and feel of traditional circline fluorescent tube flushmount fixtures, but operate at a significantly lower wattage. A CCT selection switch allows the installer to switch between 3000K, 4000K, or 5000K color temperatures. Fixtures are available in multiple diameter options in both a round profile, making the choice easy for any type of application. Installation is quick and simple when mounting into standard ceiling junction boxes, and may be installed on circuits with standard wall dimmers. Constructed with a durable steel housing body and LED lifetime rating of at least 50,000 hours, this rugged flushmount is designed for many years of reliable operation.

### Features

- Tool-less diffuser attachment
- Minimalistic and efficient design
- Mercury-free construction
- Suitable for Damp Location use
- Easy and secure installation
- TRIAC Dimmable to 10% output

### Applications

- Multi-family and Apartments
- Overhead & Hallway lighting
- Ambient room lighting
- General lighting

### Specification

Order Number	40036	40035	40034	40037
Model Number	E3LFMA22D-803050	E3MFMA14D-803050	E3SFMA12D-803050	E3XFMA32D-803050
Configuration	15" round	11" round	10" round	19" round
Beam Angle	110°	110°	110°	110°
Lumen Output	1770 LM	1115 LM	1070 LM	2490 LM
Luminous Efficacy	80 LM/W	79 LM/W	89 LM/W	77 LM/W
Input Power	22 W	14 W	12 W	32 W
Input Voltage	120 Vac	120 Vac	120 Vac	120 Vac
Power Factor	0.99	0.98	0.98	0.99
THD	<0.2	<0.2	<0.2	<0.2
Color Temp (CCT)	3000K, 4000K, 5000K Select K	3000K, 4000K, 5000K Select K	3000K, 4000K, 5000K Select K	3000K, 4000K, 5000K Select K
Color Rend (CRI)	85	84	84	85
Lifetime Rating	50000 hours	50000 hours	50000 hours	50000 hours
Warranty	10 Years	10 Years	10 Years	10 Years
Dimmability	Triac dimmable	Triac dimmable	Triac dimmable	Triac dimmable
Operating Temp	-4 to 104 (°F)	-4 to 104 (°F)	-4 to 104 (°F)	-4 to 104 (°F)
Environment	Damp Location	Damp Location	Damp Location	Damp Location
Energy Star	Energy Star	Energy Star	Energy Star	Energy Star
Safety Cert	UL	UL	UL	UL
Weight	3 LBS	1.5 LBS	1 LBS	4.5 LBS
Dimensions	15x3.5x (in)	11x3x (in)	10.2x2.7x (in)	19x4.4x (in)

## Dimensions and Packaging Info

Model Number	E3LFMA22D-803050	E3MFMA14D-803050	E3SFMA12D-803050	E3XFMA32D-803050
Item UPC	845940008439	845940008422	845940008415	845940008446
Case UPC	10845940008436	10845940008429	10845940008412	10845940008443
Master Carton UPC				
Item(s) per pack	1 per pack	1 per pack	1 per pack	1 per pack
packs per case	4 per case	4 per case	8 per case	2 per case
Case per Master				
Item weight	3 LBS	2 LBS	2 LBS	5 LBS
Case weight	15 LBS	9 LBS	14 LBS	12 LBS
Master Weight				
Item pack dimensions	17x17x5 (in)	13x13x4.5 (in)	11x11x4.5 (in)	20.5x20.5x6 (in)
Case dimensions	21x18x18 (in)	19x14x14 (in)	24x18x12 (in)	22x22x12 (in)
Master dimensions				