

Mounting Instructions

Instrucciones de montaje
Instructions de pose

ProHANGER Model No. 30330

ProHANGER Modelo núm. 30330

ProHANGER Modèle n° 30330



End Cap
Tapa lateral
Embout

Load Capacity — 75 lbs.

Capacidad de carga — 75 lbs. (34kg)

Capacité de charge — 34 kg (75 lbs.)

Preferred Screw Head Styles for ProHANGER
Estilos de cabeza de los tornillos para el ProHANGER
Types de tête de vis préférables pour ProHANGER



Hex
Washer-Faced
Hexagonal con
arandela
Hexagonale à
embase



Mushroom
(Truss)
Hongo
(segmentada)
Bombée



Pan
Redonda
Cylindrique
bombée

**3 - #14 or 1/4 inch
screws preferred**

3 tornillos núm. 14
o de 1/4 de pulgada,
preferiblemente

3 - vis n° 14 ou 1/4
pouce de préférence

