



Bollards

MEMAPLEX™



Technical Information	
Tested to withstand force of	175kN
Vehicle weight equivalent	12,000 lbs
Vehicle equivalent speed	4mph
Equivalent angle of impact	90°
Material Properties	Value
Chemical Resistance	Excellent – ISO/TR 10358
MEMAPLEX™ Operating Temperature	14°F to 122°F
MEMAPLEX® Operating Temperature	-40°F to 68°F
Environment	Value
CO2/kg	35.63 each (4ft)
Recyclability	100%
Other	Value
Standard Warranty	5 years*



A Scientific Approach to Safety

www.asafe.us

*Terms and conditions apply