



Look. Performance. Confidence.

Catalog Number
Notes
Type



A-SERIES LED Lamps

ALCND LED Candle Lamp

Decorative (A-SERIES)



FEATURES & SPECIFICATIONS

INTENDED USE

Accent lighting applications where color, dimmability, extended lamp life and efficacy are important.

CONSTRUCTION

Housing: High quality, cast aluminum, advanced thermal design for optimal cooling efficiency.

Optics: Optimally engineered for dimmable, omni-directional 340° beam spread.

EXPECTED LIFE

50,000 hours.

LUMEN OUTPUT

250 lumens (5 Watts)

Operating Temperature: -22°F to 104 °F (-30 °C to +40 °C)

Color Temperature (CRI): 2800K (82CRI)

ELECTRICAL SYSTEM

Uses High Brightness LED mounted to efficient thermal transfer system.

5-watt (250L) high efficiency integral driver 110-120VAC.

Actual wattage may differ by +10%/-15% when operating between 110-120V +/- 10%.

Dimmable down to 10%. Contact factory for dimming compatibility.

LISTING

UL/CUL certified to U.S. and Canadian safety standards

Damp location listed.

Tested in accordance with IESNA LM-79 standards.

Suitable for use in totally enclosed fixtures per UL1993.

WARRANTY

Five-year limited warranty. Complete warranty terms located at:

http://www.acuitybrands.com/Customer-Resources/Terms_and_conditions.aspx

DIMENSIONS

Diameter: 1.61"

Length: 4.29"

Weight: 0.11 lbs

All dimensions are inches.

Note: Specifications subject to change

without notice. Actual performance may

differ as a result of end user environment and

application.

ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: ALCND 250L FSG DIM

LED LAMP											
Series		Lumen output ¹		Glass Color		Dimming		Color temperature		Base	
ALCND	LED Candle Lamp	250L	5W, 250 lumens	FSG	Frosted smooth glass	DIM	Dimmable	(blank)	2800K	(blank)	E12 base
				CSG	Clear smooth glass						

Notes

1 Total system delivered lumens.



ALCND — LED Candle Lamp

OMNI DIRECTIONAL (A-SERIES)

PHOTOMETRICS

