

AMERIVAP® SYSTEMS

Clean is in the Details

MINIMUM AMP REQUIREMENT FOR 3 PHASED XTREME STEAM UNITS

INDUSTRIAL

	208	220	230	240		360	380	400	415	440	460	480	550		575	600
9kw	25	-	-	24		-	-	-	-	12	-	11	-		-	-
19.5kw	55	-	-	47		-	-	-	-	26	-	24	-		20	-

INDUSTRIAL STANDARD

	200 -210V	220-240V	360-380V	390-415V	420-440V	450-480V	550-600V
10kw	26.69 - 28.02	22.05 - 24.06	16.01 - 16.9	13.03 - 13.87	12.53 - 13.12	11.28 - 12.03	8.82 - 9.62
20kw	53.38 - 56.05	44.1 - 48.11	32.03 - 33.81	26.06 - 27.73	25.05 - 24.06	22.55 - 24.06	17.64 - 19.25
30kw	80.07 - 84.07	66.15 - 72.17	48.04 - 50.71	39.09 - 41.06	37.58 - 41.6	33.83 - 36.08	26.46 - 28.87
40kw	-	-	57.58 - 60.77	52.3 - 55.65	50.1 - 52.49	45.11 - 48.11	35.28 - 38.49
50kw	-	-	71.97 - 75.97	65.37 - 69.56	62.63 - 65.61	56.38 - 60.14	44.1 - 48.11
60kw	-	-	86.36 - 91.16	78.44 - 83.47	75.15 - 78.73	67.66 - 72.17	52.92 - 57.74
80kw	-	-	-	-	93.94 - 98.41	84.57 - 90.21	66.15 - 72.17

INDUSTRIAL TRU-BLU AMPS

	200-210V	220-240V	360-380V	390-415V	420 - 440V	450-480V	550-600V
10kw (Tru-Blu)	37.11 - 38.96	33.51 - 36.56	22.28 - 23.52	19.82 - 21.09	17.99 - 18.85	17.14 - 18.28	13.4 - 14.62
20kw (Tru-Blu)	63.8 - 66.99	55.56 - 60.61	38.3 - 40.43	32.85 - 34.96	30.52 - 31.97	28.4 - 30.31	22.22 - 24.25
30kw (Tru-Blu)	90.49 - 95.01	77.61 - 84.67	54.31 - 57.33	45.88 - 48.83	43.04 - 45.09	39.69 - 42.33	31.05 - 33.87
40kw (Tru-Blu)	-	-	75.68 - 79.88	71.91 - 76.52	65.89 - 69.03	62.02 - 66.15	48.51 - 52.92
50kw (Tru-Blu)	-	-	90.07 - 95.08	84.98 - 90.43	78.41 - 82.15	73.3 - 78.18	57.33 - 62.55
60kw (Tru-Blu)	-	-	-	-	90.94 - 95.27	84.57 - 90.21	-
80kw (Tru-Blu)	-	-	-	-	-	-	79.39 - 86.60

COMMERCIAL

AMPS REQUIREMENT SINGLE PHASE

	120 V	208 V
STEAMAX	15	
VAPOR BLITZ I	15	
VAPOR BLITZ II	15	
BLITZER	15	
3.3 KW		15