

 Cut-Resistant



# HyFlex® 11-624 Glove



Advanced Cut Protection  
Never Felt This Good.

### **Safety and comfort combined.**

No other glove offers the dynamic mix of protection and comfort of the HyFlex® 11-624 glove. The ANSI Level 2 protection and lightweight ergonomic fit strike the perfect balance of protection and precision when working with small, sharp parts.

### **Maximize safety and productivity.**

The HyFlex 11-624 glove is an effective way to decrease injury expenses without reducing productivity or quality. That's because it combines superior cut protection, abrasion resistance, grip, tactility, and dexterity in a comfortable glove your workers are more likely to wear.



  
**HyFlex**®  
Precision Protection™

# HyFlex® 11-624 Glove

## Outstanding Product Attributes & Benefits

### Dyneema® engineered yarn composition with ergonomic design

- Offers user unmatched combination of comfort, softness, coolness and cut protection
- Advanced yarn technology increases worker confidence while on the job

- ANSI Level 2 cut protection
- Soft and cool to the skin for all-day comfort
- Molds naturally to the hand, preventing fatigue while providing comfort
- Exclusive yarn combination provides exceptional precision, dexterity and flexibility when handling small parts
- Extensive size range protects more workers (6-11)

### Black Polyurethane Coating

- Proprietary black polyurethane coating provides a sure grip in light oil and dry applications
- Sure grip of product increases worker assurance when handling sharp objects
- Good resistance to tears and punctures that might occur when handling sharp parts in dry and light oil applications
- Black palm coating hides soil providing longer wear and reducing overall replacement costs

### Durable and Launderable

- Polyurethane coating provides excellent abrasion vs. other coatings
- Product can be washed and re-used without any loss of cut protection
- Minimal shrinkage, excellent recovery extends wear life
- Ability to launder reduces total cost of ownership

### Ordering Info: Sizes & Packaging


Sizes: XS (6), S (7), M (8), L (9), XL (10) & XXL (11)  
12 dozen per inner bag of 12 pairs—144 pairs per case

### Ansell HyFlex Line

The HyFlex 11-624 glove is part of the HyFlex Cut-Resistant range. The HyFlex glove line is comprised of four premium performance ranges: Precision, Cut-Resistant, Oil-Repellent, and Specialty products. Products that provide "cut resistance" and "cut protection" do not completely prevent or eliminate the potential for cuts and punctures, and are not intended or tested to provide protection against powered blades or other sharp or rotating equipment. Users are encouraged to always use caution and care when handling sharp metals. For a comprehensive review of our HyFlex Precision Protection™ line, please visit [www.hyflex.com](http://www.hyflex.com) or call 1-800-800-0444 to speak to a customer service representative.

[www.hyflex.com](http://www.hyflex.com)

Ansell and HyFlex are Registered trademarks owned by Ansell Limited or one of its affiliates. HyFlex Precision Protection™ is a trademark owned by Ansell Limited or one of its affiliates. Dyneema® is a registered trademark of Royal DSM N.V. All companies and products are trademarks of their respected owners. Printed in U.S.A. ©2007 Ansell Limited. All Rights Reserved.



### Industries

- Aerospace
- Automotive
- Electronics & Electrical
- Glass Products
- Metal Fabrication
- Paper Manufacturing
- Plastic & Rubber Manufacturing
- Tier One
- White/Durable Goods

### Applications

- Final & sub-assembly areas when handling sharp metal components
- Forming, machining & bending of small sharp parts
- Glass handling & installation
- Small part stamping
- Wiring



Ansell  
**HyFlex**®  
Precision Protection™