

JXN4, BXN4



Hi-Visibility Flame-Resistant Rainwear

Fabric: **JXN4** – 10.0 oz. (340 g/m²) Polyurethane on a knit FR treated Cotton
BXN4 – 10.0 oz. (340 g/m²) Polyurethane on a knit FR treated Cotton

Protection: **JXN4** –Arc Rating ATPV 19.0 calories/cm², Ebt 28 calories/cm² (HRC2)
BXN4 –Arc Rating ATPV 19.0 calories/cm², Ebt 28 calories/cm² (HRC2)
ASTM F 1891-06 Arc and Flame-resistant
ASTM F 2733 Flash Fire Hazard
ANSI/ISEA 107-2010

Features: Non-conductive durable hardware. 2” reflective striping. Two patch pockets with flaps. Vented back with “D” ring access. Take-up tabs on cuffs. Elasticized shoulder straps w/ non-conductive adjustable hardware. Take-up tabs at ankles.

Colors: **JXN4**– Yellow/ Green (YE)
BXN4 – Yellow/ Green (YE)



JXN4, BXN4



Stowaway hood and adjustable hood drawstring

BULWARK LABEL ADDED AT THE VENDOR

Non-conductive hard wear

360 degree reflective trim for visibility

CSA compliant

Take-up tabs for easy adjustment

The Consumer:
-Manufacturing Industry
-Oil and Gas Industry

