

CPWplus M

CPWplus

CPWplus L



* CPWplus P and W not shown

CPWplus Weighing Scales

CPWplus bench and floor scales provide exceptional value and numerous features to meet the demands of industrial, warehouse, office, field and laboratory settings. This series of scales offers an extensive range of models and configurations to accommodate a variety of applications. Choose the basic CPWplus for compact portability, the CPWplus-P version with pillar mounted display, the CPWplus-M or CPWplus-L for large platforms, or the CPWplus-W with handlebars and wheels. Simple operation, a selection of stainless steel platform sizes, battery and AC operation, and rugged construction all combine to make the CPWplus truly a great value in this industrial range.



CPWplus Weighing Scales

Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Programmable backlight can be set to “always on”, “always off” or “light only when weighing”
- Color-coded keys facilitate quick recognition of the most frequently used buttons
- Large, type 304 stainless steel pan allows swift cleaning
- Lightweight design simplifies transport and portability
- Rugged construction stands up to industrial use
- Splash-proof housing, keypad and display mean easy cleaning and peace of mind

- Wall-mount bracket for placing indicator on vertical surface
- Auto power-off to save energy
- External calibration allows for verification and adjustment with weights
- Hold function freezes the displayed weight, allowing time to lapse without losing the result
- Selectable digital filtering helps minimize effects of vibration and disturbances
- Zero-tracking feature ensures display returns to zero reading

Applications

- Weighing
- Display hold

Model	CPWplus 6	CPWplus 15	CPWplus 35	CPWplus 75	CPWplus 150	CPWplus 200	
	CPWplus 6P	CPWplus 15P	CPWplus 35P	CPWplus 75P	CPWplus 150P	CPWplus 200P	
			CPWplus 35W	CPWplus 75W	CPWplus 150W	CPWplus 200W	
			CPWplus 35M	CPWplus 75M	CPWplus 150M	CPWplus 200M	
			CPWplus 35L	CPWplus 75L	CPWplus 150L	CPWplus 200L	CPWplus 300L
Capacity	13lb / 6kg	33lb / 15kg	75lb / 35kg	165lb / 75kg	330lb / 150kg	440lb / 200kg	660lb / 300kg
Readability	0.005lb / 0.002kg	0.01lb / 0.005kg	0.02lb / 0.01kg	0.05lb / 0.02kg	0.1lb / 0.05kg	0.1lb / 0.05kg	0.2lb / 0.1kg
Repeatability (S.D.)	0.005lb / 0.002kg	0.01lb / 0.005kg	0.02lb / 0.01kg	0.05lb / 0.02kg	0.1lb / 0.05kg	0.1lb / 0.05kg	0.2lb / 0.1kg
Linearity (+/-)	0.01lb / 0.004kg	0.02lb / 0.01kg	0.04lb / 0.02kg	0.1lb / 0.04kg	0.2lb / 0.1kg	0.2lb / 0.1kg	0.4lb / 0.2kg
Tare Range	Full range						
Pan Size	11.8"x11.8" / 300x300mm 19.7"x19.7" / 500x500mm (W & M) 35.4"x23.6" / 900x600mm (L)						
Weighing Units	kg, lb, lb:oz, oz						
Stabilization Time (sec)	2						
Interface	RS-232						
Calibration	External calibration						
Display	Backlit LCD with 0.9" / 22mm-high digits						
Power Supply	12VAC 150mA adapter / 6 x AA batteries 12VDC 500mA adapter / Internal rechargeable battery (W, M & L)						
Operating Temperature	0° to 40°C / 32° to 104°F						
Housing	Extruded aluminum						
Overall Dim.	11.8"x11.8"x2" / 300x300x50mm 19.7"x22"x41.3" / 500x560x1050mm (W) 19.7"x19.7"x1.6" / 500x500x40mm (M) 35.4"x23.6"x3.1" / 900x600x80mm (L)						
Net Weight	8.82lb / 4.00kg 27.33lb / 12.40kg (W) 19.62lb / 8.90kg (M) 31.74lb / 14.40kg (L)						

NA-2127 ©Adam Equipment. All Rights Reserved.

For more than 40 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Supplied by:

ACCESSORIES

700100099	Hard carrying case w/ lock
1120011156	ATP thermal printer
3126011263	Thermal paper for item no. 1120011156-ATP printer
3126011281	Thermal paper for item no. 1120011156-ATP printer (pack of 10)
700200059	Rubber Non-Slip Mat for CPWplus L Only
3074010266	RS-232 cable (null-modem)
3074010507	RS-232 to USB adapter (must order corresponding RS-232 cable)
600002028	Adam DU software