

510 CADDY® EZ RISER

5100150EG



Features

- Recommended for suspending vertical steel pipe risers
- Slotted holes make assembly easy, eliminating loose hardware
- Serrated flange-head bolts eliminate need for wrenches on both bolt and nut
- Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 8)

Product Specifications

Part Number	5100150EG
Material	Steel
Finish	Electro-galvanized
Pipe Size	1 1/2"
Outer Diameter (OD)	1.9"
Hole Size (HS)	7/16"
A	9 7/8"
B	1"
Static Load (F)	255 lb
Standard Packaging Quantity	25 pc
UPC	78285636930
UNSPSC	40141725
EAN-13	8711893089455
ETIM	EC010049

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

