

THE HOT ONE

Shop-tough and
garage worthy



- No more cold starts—fan delay feature heats the element before it begins to blow air, and the fan stays on until the heat dissipates
- Includes high-temperature safety shutoff feature
- Hi/Low switch provides wattage choice for heat output
- Six-foot cord and heavy-duty bracket for wall mount or floor stand
- Use the fan-only feature to circulate air
- Built-in adjustable thermostat
- Available in 20 amp or 30 amp models—proper receptacle required

Bring the heat to your cold garage or shop with The Hot One, our premium utility heater. With its rugged, durable design, The Hot One takes on winter year after year.

TECHNICAL INFORMATION

The Hot One 240-volt heater includes a fan switch for air circulation without heat. All units include a built-in double pole thermostat.

UL safety standards require a 3-foot minimum clearance from the front. For best performance, we recommend a 6-inch clearance from the back and top of the heater, and a 12-inch clearance from the sides.

ORDERING INFORMATION

Standard color for The Hot One heater is red with black detail. Recommended for elevations under 7,500 feet.

Includes a 6-foot cord.

RCP502S requires a NEMA 6-30 (polarized) 30-amp receptacle for operation. RCP402S requires a NEMA 6-20 (polarized) 20-amp receptacle for operation.

Please check your receptacle and/or with your electrician before purchase.

CADET 
INVITING WARMTH

cadetheat.com
855.CADET.US
Vancouver, Washington





THE HOT ONE

15-3/4"W x 17-1/2"H x 8-1/4"D



Requires a 240 volt receptacle

Includes bracket for wall mount or floor stand use


PART	MODEL	DESCRIPTION	RECEPTACLE	WATTS (HI/LOW)	VOLTS	AMPS (HI/LOW)	BTUS (HI/LOW)	WT/LBS
10288	RCP402S	Portable garage heater, red	NEMA 6-20R	4000/2667	240	16.7/11.1	13648/9100	30
10289	RCP502S	"	NEMA 6-30R	5000/3333	240	20.8/13.9	17060/11372	30



WALL MOUNT USE



RCP Heater Controls:



Thermostat Knob

Power Indicator Light

Watts Hi/Low

On/Auto Controls

Manual Reset Limit Button