

Part Number: C2015A

Revision: 9/18/2013

1C 24 AWG PVC**HOOK UP WIRE****A. CONSTRUCTION**

Conductor: #24 AWG (7/32) Tinned Copper
Insulation: .016" Wall, Polyvinyl Chloride (PVC)
Print Legend:

CAROL A 24 AWG "RU" AWM 80C VW-1 E18621-8 -- CSA LL69381 FT-1 TR64 90C -- MADE IN USA *

*NOTE: THIS PRODUCT IS MARKED 80C AS PER UL STYLE 1007, HOWEVER, IT ALSO MEETS 105C AS PER UL STYLE 1569

DIAMETERS

.023" Nom

.055" ± .003"

B. INDUSTRY APPROVALS

UL Standard 758

AWM Style 1007, 1569

CSA International

Type TR64

C. ELECTRICAL PROPERTIES

Temperature: -20°C to +105°C
Suggested Working Voltage: 300 Vrms (Max)
Conductor DCR: 27.7 Ohms/1000ft @ 20°C (Max)

D. CUSTOMER APPROVAL

Signature: _____
Date: _____