



**CUSHMAN**



**MODEL: HAULER 1200X**  
**TYPE: GAS POWERED TRUCK**  
**MODEL YEAR: 2014**  
**Part No.: 618847**

**PRODUCT SPECIFICATION**

**CONFIGURATION HIGHLIGHTS**

**Engine:** 13.5 hp (10.1 kW) Exceeds SAE J1940 Standard, 4 cycle, 24.5 ci (401 cc) single cylinder, air-cooled by Kawasaki

- **Valve Train:** Overhead valve
- **Lubrication:** Pressurized oil system, spin-on oil filter
- **Balancer:** Internal counter rotating balance shaft
- **Fuel System:** Fixed float bowl with remote pulse fuel pump
- **Ignition:** Electronic spark/magneto
- **Air Cleaner:** Replaceable dry cartridge

**Electrical:** Starter/Generator, solid-state regulator, 12 Volt maintenance free battery (425 CCA, 60 minute reserve)

**Drive Train:** Automatic, continuously variable transmission (CVT)

**Brakes:** Dual rear wheel mechanical self-adjusting drum brakes. Automatic single point park brake release with self-compensating system

**Transaxle:** Differential with helical gears, ground speed governor, forward/reverse

**Cargo Bed:** Roto-molded cross-linked polyethylene. Lifts for access to powertrain. Removable hinged multi-position tailgate requires no latch mechanism

**PRODUCT OVERVIEW**

**Dimensions**

Overall Length	113.0 in (287 cm)
Overall Width	48.5 in (123 cm)
Overall Height (No Canopy)	52.5 in (133 cm) (Top of steering wheel)
Overall Height (With Canopy)	77.0 in (196 cm)
Wheel Base	77.0 in (196 cm)
Front Wheel Track	38.0 in (97 cm)
Rear Wheel Track	38.5 in (98 cm)
Gnd Clearance @ Differential	5.3 in (15 cm)
Cargo Box Width (inside)	44.0 in (112 cm)
Cargo Box Length (inside)	36.0 in (91 cm)
Cargo Box Depth (inside)	10.5 in (27 cm)
Cargo Box Capacity	9.6 cu ft (0.27 m3)
Cargo Box material/capacity	Roto-molded poly/9.6 cu ft (0.27 m3)

**Vehicle Power**

Valve Train	Single Cylinder OHV
Horsepower (kW)	13.5 hp (10.1 kW) Exceeds SAE J1940 Std.
Electrical System	Starter/Generator. Solid State Regulator
Batteries (Qty, Type)	One, 12 Volt Maintenance Free
Key or Pedal Start	Pedal
Air Cleaner	Replaceable Dry Cartridge
Lubrication	Pressurized Oil System
Oil Filter	Spin On
Cooling System	Air Cooled
Max Fuel Volume	6.0 Gallon (22.7 L) tank
Drive Train	Continuously variable transmission (CVT)
Transaxle	Differential with helical gears
Gear Selection	Forward - Reverse
Rear Axle Ratio	11.42:1 (Forward) 15.78:1 (Reverse)

**Performance**

Seating Capacity	2 Person
Dry Weight	910 lb (415 kg)
Curb Weight	950 lb (435 kg)
Bed Load Capacity	500 lb (226 kg)
Vehicle load capacity	800 lb (360 kg)
Outside Clearance Circle	22.0 ft (6.7 m)
Intersecting Aisle Clearance	N/A
Speed (Level Ground)	17 mph ± 0.5 mph (27.4 kph ± 0.8 kph)
Towing Capacity	500 lb (225 kg) max load

**Steering & Suspension**

Front Suspension	Leaf springs with hydraulic shock absorbers
Rear Suspension	Leaf springs with hydraulic shock absorbers
Service Brake	Rear wheel mechanical self-adjusting drum
Parking Brake	Self-compensating, single point engagement
Front Tires	Stryker 22 x 9 - 10 Uni-Directional
Rear Tires	Stryker 22 x 9 - 10 Uni-Directional

**Body & Chassis**

Frame	Welded steel. DuraShield™ powder coat
Front Body & Finish	Injection Molded TPO
Rear Body & Finish	Steel. Base coat/clear coat
Standard Color	Patriot Blue

*Some items shown may be optional equipment*



**OPTIONS & FIELD INSTALLED ACCESSORIES (Installation not included)\***

Item	Std	Opt	Fld
<b>TIRES &amp; WHEELS:</b>			
Stryker 22 x 9 - 10 Uni-directional	X		
Turf Saver 20 x 10 -10 (Load Range b)		X	
Terra Trac 22 x 11 -10 with Polished 4-Spoke Wheels		X	
<b>COLORS:</b>			
Body Color - Patriot Blue	X		
Body Color - Forest Green		X	
Body Color - Bright White		X	
Body Color - Yellow		X	
Body Color - Black		X	
Custom Body Color		X	
<b>SEATS:</b>			
Seat Color - Gray	X		
Seat Color - Oyster		X	
Seat Color - Tan		X	
Seat Color - White		X	
Seat Color - Brown		X	
Seat Color - Black		X	

Item	Std	Opt	Fld
<b>HAULING &amp; TOWING:</b>			
2 in (5 cm) Receiver (Front)			X
2 in (5 cm) Receiver (Rear)	X		
1 7/8 in (48 mm) Ball (Rcvr Req'd)		X	
Angle Hitch (Rcvr Req'd)		X	
Clevis Hitch (Rcvr Req'd)		X	
Angle Hitch, Drop (Rcvr Req'd)		X	
1 7/8 in (48 mm) Ball Hitch, Drop (Rcvr Req'd)		X	
Clevis Hitch, Drop (Rcvr Req'd)		X	
Poly Bed w/Manual Dump	X		
Poly Bed w/Elec Dump		X	
Aluminum Bed w/Manual Dump		X	
Aluminum Bed w/Electric Dump		X	
No Bed option		X	

Item	Std	Opt	Fld
<b>OTHER PERFORMANCE:</b>			
Ash Tray			X
Differential Guard		X	
Front Fascia & Brush Guard (Black)	X		
Glove Box Door (Locking) Driver Side		X	
Glove Box Door (Locking) Passenger Side		X	
Remote Air Intake		X	
State of Charge Meter		X	

Item	Std	Opt	Fld
<b>TRANSAXLE:</b>			
Limited Slip Differential		X	
High Altitude Jetting		X	

Item	Std	Opt	Fld
<b>ELECTRICAL:</b>			
Headlights	X		
Unique Individual Key Switch		X	
LED Headlights		X	
Taillights		X	
Brake Lights		X	
Turn Signals with 4-Way Flashers		X	
Strobe Light		X	
Fuel Gauge	X		
Horn	X		
Low Oil Indicator	X		
12 Volt Outlet		X	
Heavy duty battery		X	
Hour Meter		X	
CE Kit		X	

Item	Std	Opt	Fld
<b>WEATHER PROTECTION:</b>			
Sun Canopy (Top) Black			X
Canopy Handle			X
Windshield Fold Down			X
Windshield Flat			X
Weather Enclosure - Black			X
Weather Enclosure - Gray			X
Weather Enclosure - Green			X
Weather Enclosure - White			X
Weather Enclosure - Tan			X

Item	Std	Opt	Fld
<b>VEHICLE CAB:</b>			
Steel Cab (Tan):			X
Steel Cab (White):			X
Steel Cab (Non Standard Color):			X
Doors (Steel) White (Cab req'd)			X
Doors (Steel) Tan (Cab req'd)			X
Doors (Steel) Non Standard Color (Cab req'd)			X
Beacon, Amber (Cab, Fuse Panel w/Switches req'd)			X
Defroster/Fan (Cab, Fuse Panel w/Switches req'd)			X
Dome Light (Cab, Fuse Panel w/Switches req'd)			X
Doors (Vinyl) various colors (Cab req'd)			X
Rear View Mirror (Cab req'd)			X
Strobe Light (Cab, Fuse Panel w/Switches req'd)			X
Windshield Wiper (Cab req'd)			X
Curtis Cab Mirrors			X
Work Light (Cab, Fuse Panel w/Switches req'd)			X
Fuse Panel w/Switches			X