

SEWL

Wet Location/NEMA 4X Die-cast

EXIT SIGNS



FEATURES

- Exit sign for wall mounting in harsh applications or industrial environments
- Heavy-gauge, corrosion resistant and gasketed die-cast aluminum housing
- Spectron® self-test/self-diagnostic circuitry
- Vandal resistant polycarbonate shield, with tamper resistant stainless steel screws
- Universal end/ceiling/wall mount and included die-cast aluminum canopy
- Energy saving, long-life LED lamps exceed brightness and uniformity requirements
- Completely concealed break out chevron arrows; 6" letters with 3/4" stroke
- Maintenance-free, nickel-cadmium battery with fully automatic charger
- Temperature range: -30°C to 50°C (-22°F to 122°F)
- Certified to UL 924 Wet Location Standards; optional IP66; Nema 4X rating

ORDERING INFORMATION

SEWL					
MODEL	FACES	LETTER COLOR	EXIT HOUSING COLOR	OPERATION	OPTIONS
SEWL	S Single D Double	R Red G Green	B Black W White	Blank AC Only E Emergency	HTR Internal heater ¹ 4X NEMA 4X rating ²

¹For use with emergency models only.
²Heater comes standard with 4X option on emergency models.

ELECTRONICS

- Transformer isolation, surge, transient, and low voltage disconnect protection
- Pre-stripped pigtail leads with push in wiring connectors
- 90 minute emergency operation
- Reverse polarity, short circuit and AC lockout protection
- 120/277VAC 60Hz operation, test switch and LED AC-On indicator light

POWER CONSUMPTION

	120VAC	277VAC
Red AC Only Models	2.6W	2.6W
Green AC Only Models	2.1W	2.1W
Red Emergency Models	8.7W	8.4W
Green Emergency Models	8.3W	8.1W

Wattage figures include LED lamps, transformers, heaters with emergency models and electronics power requirements. LED lamp assemblies (red or green) consume less than 1 watt.

Power factor, average: .95 (lagging)

