

## COMMERCIAL-DUTY HAND DRYERS

### SELECTION guide

#### INTELLIGENT, HIGH-EFFICIENCY AND HIGH SPEED HAND DRYERS

6PGK6 series high-speed hand dryers are the most energy efficient, durable, hygienic hand dryers on the market today. Completely dries hands in 10 seconds and uses only 12% energy of traditional hand dryers. Intelligent 3 speed and on/off heating controls for customized performance to fit any application environment. Dryers' proprietary motor technology offers 2-3 times longer service life than competitive high speed dryers. Multi-port nozzle for a comfortable dry. Dryers are ideal for high traffic area.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON INTELLIGENT HIGH -SPEED HAND DRYER</b>							
<b>6PGK6</b>	Multi-port	Aluminum	Polished Chrome	Automatic	120 V	10	10 sec.
<b>6PGK7</b>	Multi-port	Stainless Steel	Polished	Automatic	120 V	10	10 sec.
<b>6PGK8</b>	Multi-port	Stainless Steel	Brushed	Automatic	120 V	10	10 sec.
<b>6PGK9</b>	Multi-port	Aluminum	White Epoxy	Automatic	120 V	10	10 sec.



6PGK6

#### HIGH SPEED VERTICAL HAND DRYERS

19UC76 is a 'hands in' vertical style high speed hand dryer featuring a HEPA filter system, wider hand drying cavity opening and antimicrobial technology. Dedicated water collection reservoir eliminates water from collecting on the floor resulting in reduced maintenance. Polarized plug for easy installation eliminating the need to hard wire. Quiet operation is ideal for sound sensitive areas.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>Dayton High -Speed Vertical Hand Dryer</b>							
<b>19UC76</b>	Vertical hand-in	High Impact ABS	Silver	Automatic	120 V	10	10-12 sec.



19UC76

#### SURFACE-MOUNTED ADA COMPLIANT HAND DRYERS

The fastest and most energy efficient surface-mounted ADA compliant hand dryer. 22UZ65 - 22UZ68 hand dryers provide the best drying performance in its class, and are perfect for all commercial washrooms. The ON/OFF heating control, stylish low-profile design with flexible cover options, and universal voltage features fits any washroom environment.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON SURFACE-MOUNTED ADA COMPLIANT HAND DRYER</b>							
<b>22UZ65</b>	Integral	Aluminum	Polished Chrome	Automatic	120/208/230V	8.3/3.7/4.1	15 sec.
<b>22UZ66</b>	Integral	Aluminum	Brushed Chrome	Automatic	120/208/230V	8.3/3.7/4.1	15 sec.
<b>22UZ67</b>	Integral	Stainless Steel	Brushed	Automatic	120/208/230V	8.3/3.7/4.1	15 sec.
<b>22UZ68</b>	Integral	Aluminum	White Epoxy	Automatic	120/208/230V	8.3/3.7/4.1	15 sec.



22UZ66

## HIGH SPEED HAND DRYERS

3NXE5 and 3NXE6 is an energy efficient, hygienic and fast automatic hand dryer. Dryers are GreenSpec listed and manufactured with antimicrobial technology inhibits growth of bacteria, mold and fungus and extends the dryer's service life. Multi-jet nozzle maximizes drying effectiveness and comfort. Its modern sleek design complements any washroom décor.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON HIGH -SPEED HAND DRYER</b>							
<b>3NXE5</b>	Multi-port	Aluminum	White Epoxy	Automatic	120 V	9.6	12 sec.
<b>3NXE6</b>	Multi-port	Aluminum	Chrome Polished	Automatic	120 V	9.6	12 sec.



3NXE6

## INDUSTRIAL HIGH OUTPUT HAND DRYERS

This series hand dryer is the industry standard for high speed hand dryers. Available in automatic or push-button. Longest life of all high speed hand dryers. Durable and vandal resistant porcelain enamel finishes. Stationary nozzle can be adjusted to swivel. Dryers are GreenSpec listed. Runs 2X faster and uses only 50% of the energy of standard dryers.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON INDUSTRIAL HIGH OUTPUT HAND DRYER</b>							
<b>4ZA64</b>	Swivel	Cast Iron	Porcelain Enamel	Push Button	120 V	20	15 sec.
<b>4ZA65</b>	Swivel	Cast Iron	Porcelain Enamel	Push Button	208/230 V	10/10	15 sec.
<b>1GVL5</b>	Fixed	Cast Iron	Porcelain Enamel	Automatic	120 V	20	15 sec.
<b>3NXE9</b>	Fixed	Steel	Epoxy Enamel	Automatic	120 V	20	15 sec.



1GVL5,



4ZA64,

## INDUSTRIAL DURABLE & VANDAL-RESISTANT HAND DRYERS

Industry standard hand dryers with the longest motor life of all hand dryers in the market. Low sound level. Durable and vandal resistant porcelain enamel finishes won't break, dent or scratch. Automatic or push-button operation. Stationary nozzle can be adjusted to swivel on push button models. 1GVL6 & 1GVL7 are recess mounted units and ADA compliant.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON INDUSTRIAL DURABLE &amp; VANDAL-RESISTANT HAND DRYER</b>							
<b>3NXE7</b>	Fixed	Steel	Epoxy Enamel	Push Button	120 V	20	30 sec.
<b>5W630</b>	Swivel	Cast Iron	Porcelain Enamel	Push Button	120 V	20	30 sec.
<b>5W631</b>	Swivel	Cast Iron	Porcelain Enamel	Push Button	208/230 V	9/10	30 sec.
<b>5W632</b>	Fixed	Cast Iron	Porcelain Enamel	Push Button	120 V	20	30 sec.
<b>5W633</b>	Fixed	Cast Iron	Porcelain Enamel	Push Button	208/230 V	9/10	30 sec.
<b>3NXE8</b>	Fixed	Steel	Epoxy Enamel	Automatic	120 V	20	30 sec.
<b>6H009</b>	Fixed	Cast Iron	Porcelain Enamel	Automatic	120 V	20	30 sec.
<b>1GVL6</b>	Fixed	Cast Iron	Porcelain Enamel	Push Button	120 V	20	30 sec.
<b>1GVL7</b>	Fixed	Cast Iron	Porcelain Enamel	Automatic	120 V	20	30 sec.



3NXE8,  
6H009

3NXE7, 5W630, 5W631,  
5W632, 5W633



1GVL7



1GVL6



## COMMERCIAL SURFACE MOUNTED LOW PROFILE HAND DRYERS

Surface-mounted economical hand dryers. Ultra compact design fits smaller size washrooms. Low sound level. 3BU95 and 3BU99 are universal voltage units that fit most electric supplies. 1GVL8 has a 6 foot long cord and 3-prong conductor plug offering hassle free quick installation. 3BU95 is ADA compliant.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON COMMERCIAL SURFACE MOUNTED LOW PROFILE HAND DRYER</b>							
<b>3BU95</b>	Integral	Aluminum	Epoxy Enamel	Automatic	120/208/230 V	10/6/5	30 sec.
<b>3BU99</b>	Integral	Steel	Epoxy Enamel	Automatic	120/208/230 V	20/11/10	30 sec.
<b>1GVL8</b>	Integral	Aluminum	Epoxy Enamel	Automatic	120 V	10	30 sec.



## COMMERCIAL LOW SOUND HAND DRYERS

Extremely low sound level. Excellent for light traffic and sound sensitive facilities. Long-life brushless motor, so no need for brush replacement. Internal thermostat for auto-off safety. Tamper resistant screws lock cover securely to base.

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
<b>DAYTON COMMERCIAL LOW SOUND HAND DRYER</b>							
<b>5W634</b>	Fixed	Aluminum	Brushed Chrome	Push Button	120 V	17	30 sec.
<b>5W635</b>	Fixed	Aluminum	Brushed Chrome	Push Button	208/230 V	7.5/8.5	30 sec.
<b>6H010</b>	Fixed	Aluminum	Brushed Chrome	Automatic	120 V	17	30 sec.
<b>1GVL9</b>	Fixed	Aluminum	Epoxy Enamel	Automatic	120 V	18	30 sec.



Find it at Grainger.

Call or visit your local branch or go to [grainger.com/dayton](http://grainger.com/dayton) for complete product line information.

**Dayton**<sup>®</sup>