

● = Least ●●●● = Most ✓ = YES * This model is available with both 15 A and 20 A



= Universal Voltage (110 - 240 V)



= ADA Compliant

	Aluminum	Stainless Steel	Steel	Cast Iron
Vandal Resistance	●●●	●●	●●	●●●●
Corrosion Resistance	●●●	●●●●	●●	●●

	6PGK6, 6PGK7, 6PGK8, 6PGK9	19UC76	22UZ65, 22UZ66, 22UZ67, 22UZ68	3NXE5, 3NXE6	4ZA64, 4ZA65, 1GVL5, 3NXE9	3NXE7, 5W630, 5W631, 5W632, 5W633, 3NXE8, 6H009, 1GVL6, 1GVL7	3BU95, 3BU99	1GVL8	1GVL9	6H010	5W634, 5W635
Fast Dry Time	●●●●	●●●●	●●●●	●●●●	●●●●	●●	●●	●●	●●	●●	●●
Energy Efficient	●●●●	●●●●	●●●●	●●●●	●●●●	●●	●●	●●	●●	●●	●●
Surface Mounted	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Recess Mounted*	✓ w/ kit			✓ w/ kit	✓	✓					
ADA Compliant	✓ w/ kit 	✓ 	✓ 	✓ w/ kit 	✓ recess 	✓ recess 	✓ 3BU95 				
Automatic Operation	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	
Push Button Operation					✓	✓			✓		✓
110-120 V	✓	✓	✓	✓	✓	✓*	✓	✓	✓	✓	✓
208-240 V	✓		✓	✓	✓	✓	✓		✓	✓	✓
220-240 V (50 Hz)	✓		✓	✓	✓	✓	✓		✓	✓	✓
277V						✓					
Universal Voltage(110-240 V)			✓ 				✓ 				
Plug-in		✓						✓			
Heated Air	✓		✓		✓	✓	✓	✓	✓	✓	✓
Speed Options	✓										
Heating Controls	✓		✓								
Antimicrobial Technology	✓	✓	✓	✓							
Qualified for LEED Credit	✓	✓	✓	✓	✓						