

# Precision Panel Convector

The PPC series smart heaters combine the advanced performance of a built-in electronic thermostat with exclusive wireless CONNEX™ technology, which provides enhanced comfort, energy-savings and easy whole-home control.

## Features

- Built-in electronic thermostat for up to 33% energy savings compared to PLX with TS521W thermostat
- Proportional heating: precisely matches heat loss to deliver maximum comfort and energy efficiency
- Controls room temperature within 0.5°C (0.9°F)
- Compatible with optional CONNEX™ wireless controls; allows for simple, whole-home control from a single device
- Learning technology: learns the room environment and adapts to maintain better comfort
- Silent operation with no moving parts
- Economy setting – reduce set temperature when room is not in use
- Manual reset high limit protection
- Detachable wall mounting bracket for easy installation and cleaning

## Applications

- Ideal for new installations or where there is an existing supply line but no wall thermostat



Built-in Electronic Thermostat

## Specifications

<b>Voltage</b>	240/208 volts
<b>Wattage</b>	500/375W, 1000/750W, 1500/1125W, 2000/1500W
<b>Color</b>	White
<b>Finish</b>	Polyester powder coated finish on body and grille
<b>Construction</b>	Attractive European designed front cover is constructed of durable 21 gauge steel. The hinged wall mounting bracket detaches from unit back for easy installation and incorporates “tilt forward” feature for cleaning. Includes built-in electronic thermostat.
<b>Heating Element</b>	Finned, steel sheathed element for durability and efficient heat transfer.
<b>Control</b>	Built-in electronic thermostat, an RF transceiver for wireless control and whole-home synchronization. Optional single-zone (DPCRWS) or multi-zone (CX-MPC) CONNEX™ Controllers are available for easy, whole-home control. CSA-C828 compliant.
<b>Warranty</b>	2-year limited warranty on complete unit; 10-year warranty on element.



## Ordering Guide

Cat. No.	Volts	Watts	A	Weight (kg/lbs.)
PPC0500	240/208	500/375	450mm (17.7")	4.2/9.3
PPC1000	240/208	1000/750	620mm (24.4")	5.6/12.4
PPC1500	240/208	1500/1125	690mm (27.2")	5.9/12.9
PPC2000	240/208	2000/1500	860mm (33.9")	7.1/15.7

## Dimensions and Installation Options

