



KEY DIMENSIONS

Case Width:	24"
Case Depth:	24"
Case Height:	48-1/2" or 64-1/4"

Right Hand configurations are shown

Features:

Flagship Storage Towers are available in two heights and three configuration types; a personal storage tower, an end tower with a bookcase and a desk tower.

Construction:

Cold rolled steel construction features bends and forming throughout components to add strength where needed for a robust construction.

Pedestal -

Welded case construction with a double 'O'-frame inner framework and welded top front corners on case. The bottom pan consists of front and rear 'O'-frame horizontal with welded dust pan to fully enclose bottom. Pedestal is secured to wardrobe, bookcase and personal storage with screws.

File and Box drawers feature double wall sides with Tog-Lok construction. File drawers have high drawer sides to accommodate hanging file folders without the need for hangrails.

Wardrobe -

Welded case construction with front, center and rear welded vertical uprights. Wardrobe is secured to pedestal, bookcase and personal storage with screws.

Personal Storage -

Four welded vertical uprights. Secured to pedestal with screws.

Bookcase -

Welded shelf supports. Secured to pedestal with screws.

Front top and bottom corners are welded. One piece top snaps on and is secured with screws.

Doors have welded stiffeners for rigidity, rubber closing bumpers at top and bottom and pulls match pedestal drawer pulls.

Finish:

Steel parts are finished with a baked enamel over a rust-inhibiting phosphate pre-treatment. All modules (pedestal, wardrobe, bookcase and personal storage) are painted individually, then assembled to one another for full paint coverage.

Personal Storage Tower

The Personal Storage tower consists of a 15" x 22-7/8" x 28" (W-D-H) pedestal combined with a wardrobe and personal storage unit. The pedestal is available in file/file or box/box/file drawer configurations. The wardrobe comes standard with hanger rod installed. The personal storage has (2) adjustable shelves on 1/2" centers. The personal storage and wardrobe have hinged doors available in right or left hand configurations.

End Tower with Bookcase

The End Tower with Bookcase consists of a 15" x 22-7/8" x 28" (W-D-H) pedestal combined with a wardrobe and side access bookcase unit. The pedestal is available in file/file or box/box/file drawer configurations. The wardrobe comes standard with hanger rod installed and a hinged door available in right or left hand configuration. The bookcase has easily adjustable shelves on 1/2" centers (2 on 64-1/4" unit, 1 on 48-1/2" unit).

Desk Tower

The Desk Tower consists of a 15" x 22-7/8" x 28" (W-D-H) pedestal combined with a wardrobe and an accessory wall. The is available in file/file or box/box/file drawer configurations. The wardrobe comes standard with hanger rod installed and a hinged door available in right or left hand configuration. The accessory wall accepts all 24" Initiate panel hung accessories (must be purchased separately), adjustable on 1" centers. The top of pedestal can support/secure freestanding or be positioned flush up to panel hung work surfaces.

The HON Company
200 Oak Street
Muscatine, IA 52761
800-833-3964
hon.com



Flagship® Storage Towers Technical Specifications

Hardware:

Nickel plated hinges, 3-way adjustable on all doors with a 110° swing.

Plastic grommets standard in pedestal work surface, bookcase and personal storage units.

Chrome plated hanger rod standard in wardrobe unit.

Three pull styles are available:

‘N’ – Full Integral Pull

‘R’ – Full Radius Pull

‘A’ – Satin Chrome Arch Pull

File drawers include a follower and a cross rail, both constructed of high impact polystyrene, and gray in color.

Box drawers include a drawer divider, constructed of high impact polystyrene, and gray in color.

A pencil tray is included in the top box drawers, constructed of high impact polystyrene, black in color.

Cable management provisions are provided in pedestal, personal storage and bookcase modules. Removable pedestal back pan provides easy access to cable management.

Glides:

Constructed of a 3/8-16 steel stem and a 2” diameter, 1/2” thick black polypropylene base, with 2” adjustment. Glides are adjustable from inside the pedestal and wardrobe unit with a hex head for 1/4” 6-point socket wrench. Glides are shipped installed.

Drawer suspension:

Take apart heavy-duty ball bearing slides with full extension on all pedestal drawers.

Locks:

Included on all models, polished chrome face locks are core removable with the ability to key alike. Each personal storage unit, wardrobe and pedestal lock independently, and all locks within one storage tower are keyed alike.

Pedestal cam lock activates a horizontal lockbar, which activates a vertical lockbar and engages the left side of the drawers when locked.

Personal storage and wardrobe doors are equipped with separate, flush, nickel plated slide locks which engage at the center of the doors directly into cabinet wall.

QUICK REFERENCE TABLE - Dimensions	Load Capacity
Overall Case Dimensions 24" x 24" x 48-1/2" or 64-1/4" (W-D-H)	N/A
Pedestal Inside Draw er Dimensions Box - 11-15/16" x 17-3/4" x 4-5/8" (W-D-H) File - 11-15/16" x 17-3/4" x 10-9/16" (W-D-H)	16.7 lbs 38 lbs
Wardrobe Inside Dimensions 64-1/4" unit: 7-1/2" x 22-7/8" x 61-1/8" (W-D-H) 48-1/2" unit: 7-1/2" x 22-7/8" x 45-5/8" (W-D-H)	N/A N/A
Personal Storage Inside Dimensions 64-1/4" unit: 13-5/16" x 23" x 35-7/16" (W-D-H) 48-1/2" unit: 13-5/16" x 23" x 19-15/16" (W-D-H)	62.5 lbs per shelf
Bookcase Inside Dimensions 64-1/4" unit: 13-5/16" x 14" x 35-1/8" (W-D-H) 48-1/2" unit: 13-5/16" x 14" x 19-5/8" (W-D-H)	38 lbs per shelf
Desk Tow er Accessory Wall Dimensions Accessory slots 23-3/16" (center to center) Accessory w all height 36" on 64-1/4" unit, and 19" on 48-1/2" unit Work surface size on top of pedestal 14-1/16" x 24" (W-D)	

Accessories:

HSTB2W1 Tower to Worksurface Brackets allows Personal Storage Towers and Bookcase towers to attach to panel hung worksurfaces and replaces the need for a panel attached end panel.

HKP2424R and HKP2424L Flush Front Kickplates mount to base of tower to provide a flush appearance to coordinate and align with laterals and file centers.

Shipping Information:

Storage towers ship assembled in a full stretch wrap package with innerpack for protection. ‘A’ pulls are installed by end user using a phillips head screwdriver.

Compliance:

Meets or exceeds applicable ANSI/BIFMA and ISTA Performance Standards.

Certified SCS Indoor Advantage™ GOLD



Flagship® Storage Towers Technical Specifications

Models:	Description:	Models:	Description:
HKP2424L	Kickplate	HST25723RN	End Tower with Bookcase
HKP2424R	Kickplate	HST25723RR	End Tower with Bookcase
HST24523LA	Personal Storage Tower	HST25823LA	End Tower with Bookcase
HST24523LN	Personal Storage Tower	HST25823LN	End Tower with Bookcase
HST24523LR	Personal Storage Tower	HST25823LR	End Tower with Bookcase
HST24523RA	Personal Storage Tower	HST25823RA	End Tower with Bookcase
HST24523RN	Personal Storage Tower	HST25823RN	End Tower with Bookcase
HST24523RR	Personal Storage Tower	HST25823RR	End Tower with Bookcase
HST24623LA	Personal Storage Tower	HST26523LA	Desk Tower
HST24623LN	Personal Storage Tower	HST26523LN	Desk Tower
HST24623LR	Personal Storage Tower	HST26523LR	Desk Tower
HST24623RA	Personal Storage Tower	HST26523RA	Desk Tower
HST24623RN	Personal Storage Tower	HST26523RN	Desk Tower
HST24623RR	Personal Storage Tower	HST26523RR	Desk Tower
HST24723LA	Personal Storage Tower	HST26623LA	Desk Tower
HST24723LN	Personal Storage Tower	HST26623LN	Desk Tower
HST24723LR	Personal Storage Tower	HST26623LR	Desk Tower
HST24723RA	Personal Storage Tower	HST26623RA	Desk Tower
HST24723RN	Personal Storage Tower	HST26623RN	Desk Tower
HST24723RR	Personal Storage Tower	HST26623RR	Desk Tower
HST24823LA	Personal Storage Tower	HST26723LA	Desk Tower
HST24823LN	Personal Storage Tower	HST26723LN	Desk Tower
HST24823LR	Personal Storage Tower	HST26723LR	Desk Tower
HST24823RA	Personal Storage Tower	HST26723RA	Desk Tower
HST24823RN	Personal Storage Tower	HST26723RN	Desk Tower
HST24823RR	Personal Storage Tower	HST26723RR	Desk Tower
HST25523LA	End Tower with Bookcase	HST26823LA	Desk Tower
HST25523LN	End Tower with Bookcase	HST26823LN	Desk Tower
HST25523LR	End Tower with Bookcase	HST26823LR	Desk Tower
HST25523RA	End Tower with Bookcase	HST26823RA	Desk Tower
HST25523RN	End Tower with Bookcase	HST26823RN	Desk Tower
HST25523RR	End Tower with Bookcase	HST26823RR	Desk Tower
HST25623LA	End Tower with Bookcase	HSTB2W1	Tower to Worksurface Bracket
HST25623LN	End Tower with Bookcase	HKP2424L	Flush Front Kickplate
HST25623LR	End Tower with Bookcase	HKP2424R	Flush Front Kickplate
HST25623RA	End Tower with Bookcase		
HST25623RN	End Tower with Bookcase		
HST25623RR	End Tower with Bookcase		
HST25723LA	End Tower with Bookcase		
HST25723LN	End Tower with Bookcase		
HST25723LR	End Tower with Bookcase		
HST25723RA	End Tower with Bookcase		

The HON Company
200 Oak Street
Muscatine, IA 52761
800-833-3964
hon.com

© 2011 The HON Company
H4010 (01/11)
HON is a registered trademark
of HNI Technologies, under
license to The HON Company.