

**XP
SERIES**

GENERAC®

XP SERIES PORTABLE GENERATORS



Professional-grade for demanding job sites

XP SERIES GENERATORS 3600 – 10000 WATTS

The undisputed workhorse of the portable market, Generac's professional grade XP Series portable generators are engineered specifically with contractors in mind. All models are powered by the Generac OHVI® engine, built to withstand extended job site use.



Fold-down, Locking Handles

Provide sturdy portability, fold down for compact storage, factory installed (XP6500E, XP8000E, XP10000E)

Integrated Lifting Eye

For easier transportation and added security on jobsites

Large Steel Fuel Tank with Integrated Fuel Gauge

For extended run time and easy fuel tracking

Hardened 1.25" Steel Tube Cradle and Cast Metal Corners

For rugged durability

Easy-to-access Maintenance Points

Makes routine maintenance easier and quicker

Never-flat Wheels

For mobility on any terrain

TRUEPOWER™ TECHNOLOGY

Delivers best-in-class power quality for confident operation of power tools, computers and more. With less than 5% total harmonic distortion, you're assured of quality and performance as smooth and consistent as utility power.



GENERAC OHVI® ENGINE

Power for Extended Performance

All models feature Generac's OHVI engine, which utilizes the same type of pressurized oil lubrication used to give automobile engines long


and trouble free lives and has a significantly longer life than many competitive engines – an unprecedented three to four times longer.



WHAT'S INCLUDED

- **3 year limited warranty**
- Wheel Kit & Handles
(Sold Separately on XP4000)
- Engine Oil Supply
- Owner's Manual
- Maintenance Kit

Easy access all-in-one control panel



On/Off Switch, Choke, Fuel Shut Off

Battery Charging Jack
To keep the battery charged and ready

Idle Control
Conserves fuel and reduces noise

GFCI Protected Covered Outlets

Hour Meter
With maintenance resets

120/240 Voltage Selector
Allows full 120V power or 120/240V power output (XP4000 & XP6500E models)

Full Panel GFCI Protection
OSHA compliant

How much power do you need?

How do you determine what size generator you need?

Sizing a portable generator is relatively easy. Check out this sample:

- 1** Choose which devices you want to power at the same time.
- 2** Record and add the running watts listed for each device that you need to power.
- 3** Record the starting watts listed for each device.
- 4** Select the one device with the highest starting watts. Add that number to the the total running watts to determine the total wattage requirement.

Device	Running Watts	Additional Starting Watts	Generator Size
Paint Sprayer	600	1200	Minimum starting watts for your needs ↓ 5800 starting watts
Halogen Light	1000	0	
Belt Sander	1200	2400	
Air Compressor -1/2HP	1000	2000	
Total	3800	+ 2000	

	Device	Running Watts	Additional Starting Watts
Jobsite	Air Compressor - 1 HP	1600	4500
	Air Compressor - 1/2 HP	1000	2000
	Airless Paint Sprayer- 1/3 HP	600	1200
	Belt Sander - 3"	1200	2400
	Bench Grinder - 8"	1400	1100
	Circular Saw - 7-1/4"	1400	2300
	Hand Drill - 1/2"	600	900
	Hand Drill - 3/8"	400	600
	Miter Saw - 10"	1800	1800
	Quartz Halogen Work Light	1000	-
	Reciprocating Saw	960	-
	Table Saw, 10"	2000	2000
	Electric Hedge Trimmer	400	-
Electric Line Trimmer - 9"	350	-	
Electric Chain Saw - 12" (1/2HP)	900	-	
Household	Computer with a 17" Monitor	800	-
	Microwave - 1000 Watts	1000	-
	Refrigerator/Freezer	700	2200
	Sump Pump 1/2 HP	1050	2150
	Television - 27"	500	-
	Well Pump - 1/2 HP	1000	2100
	Central AC - 24,000 BTU	3800	4950
	Furnace Fan Blower - 1/2 HP	875	2300
	Heat Pump	4700	4500
	Space Heater	1800	-
Window AC - 12,000 BTU	3250	3950	
Recreation	AM/FM Radio	100	-
	CD / DVD Player	100	-
	Cell Phone Battery Charger	25	-
	Inflator Pump	50	150
RV Air Conditioner (13,500 BTU)	1500	700	

*Watts listed are approximate. Check your appliance for actual requirements. Total wattage requirements assumes intermittent starting of devices.

Portable Generator Specifications

Series	XP4000	XP6500E	XP8000E	XP10000E
49-State / CSA Model #	5929	5930	5931	5932
CARB Model #	5933	5934	5935	N/A
Running Watts	3600	6500	8000	10000
Starting Watts	4500	8125	10000	12000
Engine Displacement	216cc	407cc	407cc	530cc
Engine Type	Generac OHVI	Generac OHVI	Generac OHVI	Generac OHVI
Starting Method	Recoil Pull Start	Electric/Recoil Pull Start	Electric/Recoil Pull Start	Electric
Battery Included	No	Yes	Yes	Yes
Pressure Lube with Filter	Yes	Yes	Yes	Yes
Low Oil Pressure Shutdown	Yes	Yes	Yes	Yes
Fuel Tank in gallons (liters)	4.7 (17.8)	9 (34)	9 (34)	9.2 (34.75)
Run Time at 50% Load	9.5 Hours	11 Hours	10 Hours	9 Hours
Full-Panel GFCI Protection - OSHA Compliant	Yes	Yes	Yes	Yes
Idle Control	On Control Panel	On Control Panel	On Control Panel	On Control Panel
Total Harmonic Distortion	< 5%	< 5%	< 5%	< 5%
120/240V Selector Switch	Yes	Yes	No	No
GFCI Protected Outlets	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twist Lock (1) 120/240V 30A L14-30R Twist Lock	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twist Lock (1) 120/240V 30A L14-30R Twist Lock	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twist Lock (1) 120/240V 30A L14-30R Twist Lock	(2) 120V 20A 5-20R Duplex (1) 120V 30A L5-30R Twist Lock (1) 120/240V 30A L14-30R Twist Lock (1) 125/240V 14-50R
Single-Point Lifting Eye	Included	Included	Included	Included
Handle Style	Folding/Locking (Accessory)	Folding/Locking	Folding/Locking	Folding/Locking
Wheel type	10" Solid Wheels	10" Solid Wheels	10" Solid Wheels	10" Solid Wheels
Maintenance Kit	Included	Included	Included	Included
Dimensions (L" x W" x H")	30.5 x 18.5 x 23.5	34.5 x 29 x 27.25	34.5 x 29 x 27.25	34.75 x 29 x 34
Product Weight (Pounds)	139	235	249	293
Warranty - Residential	3 Year Ltd.	3 Year Ltd.	3 Year Ltd.	3 Year Ltd.
Warranty - Commercial	2 Year Ltd.	2 Year Ltd.	2 Year Ltd.	2 Year Ltd.

All portable specifications and models subject to change. Please consult factory for availability.

HOME STANDBY GENERATORS

The Safe, Automatic Solution for Home Backup.

The power goes out and the generator goes on – whether you are home or away. It's that's simple. Install the #1 selling home standby generator from Generac and never again deal with extension cords or refuelling in a storm. Instead, enjoy safe, automatic home protection from the inconveniences and potentially dangerous effects of power outages. There's nothing like the peace of mind a Generac automatic home standby generator can give to you and your family.



AUTOMATIC 24/7 POWER PROTECTION

Portable power since 1959

Since the original portable that started it all in 1959, Generac has continued to engineer advances in standby power for more than fifty years. Generac's product range now includes power solutions from RV, portable, and automatic home standby generators to backup systems for commercial and industrial applications, all backed by an extensive nationwide service network of certified dealers. Because of our ongoing commitment to quality and innovation, Generac is the name home and business owners have come to trust.

Portable Parts and Service

Generac portable generators are supported through an extensive nationwide service network that provides parts and technical support to homeowners and contractors. For a portable generator dealer near you, visit generac.com.

GENERAC®

generac.com