

spotlight



The energy-efficient radiance of the GE energy smart® LED PAR30 short and long neck lamps is not just something you see, it's something you feel.

GE energy smart® LED PAR30 short and long neck lamps

For efficient, long-lasting options for traditional downlight applications, GE energy smart® dimmable 10-watt LED PAR30 lamps are the perfect solution.

LOW-COST OPERATION:

- Using only 12 watts of energy, save over \$104 in energy costs over the rated life of a lamp versus a standard 50-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources

EXCELLENT COLOR RENDERING

- Available with a CRI of 80 to 92

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K and 3000K

LONG LIFE

- Up to 30,000 hours rated life (L70)
- Up to 50,000 hours rated life (L70) for dimmable version

DIMMABLE

- Dims from 100% to 10%

BEAM PATTERNS

- Available in 15°, 20°, 24°, 25°, 35° and 40° beam patterns

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM



imagination at work

PERFORMANCE DATA

GE energy smart® LED PAR30 short and long neck lamps

BULB SHAPE	BASE TYPE	WATTS	GRAINGER ITEM NUMBER	ORDER CODE	DESCRIPTION	CASE VOLTS	MOL QTY	LUMENS (IN)	LUMENS INITIAL	CBCP	INITIAL COLOR TEMP	+RATED LIFE (YRS) 3HRS/DAY	*RATED LIFE (L70HRS)	*ESTIMATED ENERGY COST/YR	ENERGY STAR® STATUS	ADDITIONAL INFORMATION	
Retail PAR30 (Visual Comfort Lens™)																	
PAR30	MED	12	36M976	67922	LED12DP30R930/15	120	6	3.75	860	5650	3000	91	22.8	25,000	\$1.45	★	Accent, 15° beam, Silver
			36M977	67923	LED12DP30R930/25	120	6	3.75	860	3100	3000	91	22.8	25,000	\$1.45	★	Accent, 25° beam, Silver
			36M978	67924	LED12DP30R930/40	120	6	3.75	860	1350	3000	91	22.8	25,000	\$1.45	★	Accent, 40° beam, Silver
			36M973	67925	LED12DP30R927/15	120	6	3.75	820	5350	2700	91	22.8	25,000	\$1.45	★	Accent, 15° beam, Silver
			36M974	67926	LED12DP30R927/25	120	6	3.75	820	2950	2700	91	22.8	25,000	\$1.45	★	Accent, 25° beam, Silver
			36M975	67927	LED12DP30R927/40	120	6	3.75	820	1300	2700	91	22.8	25,000	\$1.45	★	Accent, 40° beam, Silver
Compact PAR30 (Concave Cover)																	
PAR30	MED	12	14H649	65135	LED12DP30S830/20	120	6	3.75	750	5100	3000	84	22.8	25,000	\$1.45	★	Accent, 20° beam, Silver
			14H650	65136	LED12DP30S830/35	120	6	3.75	750	2050	3000	84	22.8	25,000	\$1.45	★	Accent, 35° beam, Silver
			14H651	65137	LED12DP30S827/20	120	6	3.75	740	5000	2700	83	22.8	25,000	\$1.45	★	Accent, 20° beam, Silver
			14H652	65138	LED12DP30S827/35	120	6	3.75	740	2000	2700	83	22.8	25,000	\$1.45	★	Accent, 35° beam, Silver
			NEW	65985	LED12DP30S827/25	120	6	3.75	740	3200	2700	83	22.8	25,000	\$1.45	★	Accent, 25° beam, Silver
			36M979	65986	LED12DP30W827/25	120	6	3.75	740	3200	2700	83	22.8	25,000	\$1.45	★	Accent, 25° beam, White
			36M972	65987	LED12DP30B827/25	120	6	3.75	740	3200	2700	83	22.8	25,000	\$1.45	★	Accent, 25° beam, Black
			NEW	67256	LED12DP30S840/20	120	6	3.75	840	5800	4000	85	22.8	25,000	\$1.45	★	Accent, 20° beam, Silver
			NEW	67257	LED12DP30S840/35	120	6	3.75	840	2600	4000	85	22.8	25,000	\$1.45	★	Accent, 35° beam, Silver
Compact PAR30 (Convex Cover)																	
PAR30	MED	10	6XWJ5	61922	LED10DP30S830/20	120	6	3.75	500	3720	3000	80	45.7	50,000	\$1.20	★	Accent, 20° beam, Silver
			6XWJ6	61923	LED10DP30S827/20	120	6	3.75	450	3450	2700	80	45.7	50,000	\$1.20	★	Accent, 20° beam, Silver
			36M970	68013	LED10DP30S827/35	120	6	3.75	450	1240	2700	80	22.8	25,000	\$1.20		Accent, 35° beam, Silver
			NEW	64326	LED10DP30W827/20	120	6	3.75	450	3450	2700	80	45.7	50,000	\$1.20	★	Accent, 20° beam, White
Retail PAR30 Long Neck (Visual Comfort Lens™)																	
PAR30L	MED	12	36M983	68387	LED12DP3LR930/15	120	6	4.75	860	5650	3000	91	22.8	25,000	\$1.45		Accent, 15° beam, Silver
			36M984	68388	LED12DP3LR930/25	120	6	4.75	860	3100	3000	91	22.8	25,000	\$1.45		Accent, 25° beam, Silver
			36M985	68389	LED12DP3LR930/40	120	6	4.75	860	1350	3000	91	22.8	25,000	\$1.45		Accent, 40° beam, Silver
			36M980	68390	LED12DP3LR927/15	120	6	4.75	820	5350	2700	91	22.8	25,000	\$1.45		Accent, 15° beam, Silver
			36M981	68391	LED12DP3LR927/25	120	6	4.75	820	2950	2700	91	22.8	25,000	\$1.45		Accent, 25° beam, Silver
			36M982	68392	LED12DP3LR927/40	120	6	4.75	820	1300	2700	91	22.8	25,000	\$1.45		Accent, 40° beam, Silver
Compact PAR30 Long Neck (Concave Cover)																	
PAR30	MED	12	14H653	65139	LED12DP3LS830/20	120	6	4.75	750	5100	3000	84	22.8	25,000	\$1.45	★	Accent, 20° beam, Silver
			14H654	65140	LED12DP3LS830/35	120	6	4.75	750	2050	3000	84	22.8	25,000	\$1.45	★	Accent, 35° beam, Silver
			14H655	65141	LED12DP3LS827/20	120	6	4.75	740	5000	2700	83	22.8	25,000	\$1.45	★	Accent, 20° beam, Silver
			14H656	65142	LED12DP3LS827/35	120	6	4.75	740	2000	2700	83	22.8	25,000	\$1.45	★	Accent, 35° beam, Silver
Compact PAR30 Long Neck (Convex Cover)																	
PAR30L	MED	10	6XWJ7	61924	LED10DP3LS830/20	120	6	4.75	500	3720	3000	80	22.8	50,000	\$1.20	★	Accent, 20° beam, Silver
			6XWJ8	61925	LED10DP3LS827/20	120	6	4.75	450	3450	2700	80	22.8	50,000	\$1.20	★	Accent, 20° beam, Silver
			36M971	68014	LED10DP3LS827/35	120	6	4.75	450	1240	2700	80	22.8	25,000	\$1.20		Accent, 35° beam, Silver
Compact PAR30 - Non-Dimming (Convex Cover)																	
PAR30	MED	10	4CEX6	75613	LED10DP30S830/24	120	6	3.75	340	1400	3000	82	27.4	30,000	\$1.20		Accent, 24° Beam, Silver
			6CEA7	76144	LED10DP30S827/24	120	6	3.75	320	1300	2700	82	27.4	30,000	\$1.20		Accent, 24° Beam, Silver
Retail Display Compact PAR30 Long Neck - Non-Dimming (High CRI - Low Glare - Visual Comfort Lens™)																	
PAR30L	MED	12	16X191	66050	LED12P3LS930/25	120	6	4.75	660	3000	3000	92	22.8	25,000	\$1.45	★	Narrow Flood, 25° Beam, Silver
			16X192	66051	LED12P3LS930/40	120	6	4.75	660	950	3000	92	22.8	25,000	\$1.45	★	Flood, 40° Beam, Silver
			16X193	66052	LED12P3LS927/25	120	6	4.75	630	3000	2700	92	22.8	25,000	\$1.45	★	Narrow Flood, 25° Beam, Silver
			16X194	66053	LED12P3LS927/40	120	6	4.75	630	900	2700	92	22.8	25,000	\$1.45	★	Flood, 40° Beam, Silver

For additional product and application information, please consult GE's website: gelighting.com/ThinkLED

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original lumen rating (L70)
 ** Minimum order quantity = 6
 ★ ENERGY STAR® qualified
 ^ Estimated energy cost per year based on \$0.11 per kWh energy rate and 3 operating hours per day
 Note: Product descriptions ending in "TP" indicate a card blister or clamshell package nested in a tray for shelf display.
 Cards also designed for hook display.



Product is compliant with material restriction requirements of RoHS
 energy smart® is a registered trademark of GE
 ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks

