

spotlight



The bright white radiance of the GE energy smart® LED retail PAR30 short and long neck lamps is not just something you see, it's something you feel.

GE energy smart® LED retail PAR30 short and long neck lamps

For the perfect solution for all of your retail application needs, turn to GE energy smart® retail PAR30 lamps. With advanced optics and reduced glare, these lamps offer the light qualities desired by merchants.

LOW-COST OPERATION

- Using only 12 watts of energy, save over \$173 in energy costs over the rated life of the lamp versus a standard 75-watt halogen PAR30 lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources
- Our LED PAR lamps have less heat, UV or infrared in the beam, which reduces the potential for fading of materials and décor, compared to halogen or incandescent lamps

EXCELLENT COLOR RENDERING

- Available with a CRI of 91 to 92

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K and 3000K

LONG LIFE

- 25,000 hours rated life (L70)

DIMMABLE

- Dims from 100% to 10%

BEAM PATTERNS

- Available in 15°, 25° and 40° beam patterns

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty



Featuring GE's exclusive **Visual Comfort Lens™** for the perfect blend of enhanced color quality, advanced optics and reduced glare. Exclusive Visual Comfort Lens™ Optics create halogen-like light and contrast, with the energy and cost-efficient benefits of an LED lamp.

ecomaginationSM

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.



imagination at work

PERFORMANCE DATA

GE energy smart® LED retail PAR30 short and long neck lamps

BULB SHAPE	BASE TYPE	WATTS	GRAINGER ITEM NUMBER	ORDER CODE	DESCRIPTION	VOLTS	CASE QTY	MOL (IN)	LUMENS INITIAL	INITIAL COLOR CBCP	TEMP	CRI	+RATED LIFE (YRS) 3HRS/DAY	*RATED LIFE L70(HRS)	ESTIMATED ENERGY COST/YR	ENERGY STAR® STATUS	ADDITIONAL INFORMATION	
Retail PAR30 - Dimming (Visual Comfort Lens™)																		
PAR30	MED	12	36M976	67922	LED12DP30R930/15	120	6	3.75	860	5650	3000	91	22.8	25,000	\$1.45	★	Accent, 15° Beam, Silver	
			36M977	67923	LED12DP30R930/25	120	6	3.75	860	3100	3000	91	22.8	25,000	\$1.45	★	Accent, 25° Beam, Silver	
			36M978	67924	LED12DP30R930/40	120	6	3.75	860	1350	3000	91	22.8	25,000	\$1.45	★	Accent, 40° Beam, Silver	
			36M973	67925	LED12DP30R927/15	120	6	3.75	820	5350	2700	91	22.8	25,000	\$1.45	★	Accent, 15° Beam, Silver	
			36M974	67926	LED12DP30R927/25	120	6	3.75	820	2950	2700	91	22.8	25,000	\$1.45	★	Accent, 25° Beam, Silver	
			36M975	67927	LED12DP30R927/40	120	6	3.75	820	1300	2700	91	22.8	25,000	\$1.45	★	Accent, 40° Beam, Silver	
Retail PAR30 Long Neck - Dimming (Visual Comfort Lens™)																		
PAR30L	MED	12	36M983	68387	LED12DP3LR930/15	120	6	4.75	860	5650	3000	91	22.8	25,000	\$1.45		Accent, 15° Beam, Silver	
			36M984	68388	LED12DP3LR930/25	120	6	4.75	860	3100	3000	91	22.8	25,000	\$1.45		Accent, 25° Beam, Silver	
			36M985	68389	LED12DP3LR930/40	120	6	4.75	860	1350	3000	91	22.8	25,000	\$1.45		Accent, 40° Beam, Silver	
			36M980	68390	LED12DP3LR927/15	120	6	4.75	820	5350	2700	91	22.8	25,000	\$1.45		Accent, 15° Beam, Silver	
			36M981	68391	LED12DP3LR927/25	120	6	4.75	820	2950	2700	91	22.8	25,000	\$1.45		Accent, 25° Beam, Silver	
			36M982	68392	LED12DP3LR927/40	120	6	4.75	820	1300	2700	91	22.8	25,000	\$1.45		Accent, 40° Beam, Silver	
Retail Display Compact PAR30 Long Neck - Non-Dimming (High CRI - Low Glare - Visual Comfort Lens™)																		
PAR30L	MED	12	16X191	66050	LED12P3LS930/25	120	6	4.75	660	3000	3000	92	22.8	25,000	\$1.45	★	Narrow Flood, 25° Beam, Silver	
			16X192	66051	LED12P3LS930/40	120	6	4.75	660	1100	3000	92	22.8	25,000	\$1.45	★	Flood, 40° Beam, Silver	
			16X193	66052	LED12P3LS927/25	120	6	4.75	630	3000	2700	92	22.8	25,000	\$1.45	★	Narrow Flood, 25° Beam, Silver	
			16X194	66053	LED12P3LS927/40	120	6	4.75	630	1100	2700	92	22.8	25,000	\$1.45	★	Flood, 40° Beam, Silver	

For additional product and application information, please consult GE's website: gelighting.com/ThinkLED

- * The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original lumen rating (L70)
 - ** Minimum order quantity = 6
 - ★ ENERGY STAR® qualified
 - ^ Estimated energy cost per year based on \$0.11 per kWh energy rate and 3 operating hours per day
- Note: Product descriptions ending in "TP" indicate a card blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.



Product is compliant with material restriction requirements of RoHS
 energy smart® is a registered trademark of GE
 ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks

