

Residential Power Washers

GENERAC®

Power Washers



2500 psi - Model 006020-3 (49-State & Canada)
UPC: 696471060201

2700 psi - Model 006022-3 (49-State & Canada)
UPC: 696471060225

Model 006023-0 (50-State)
UPC: 696471060232

3100 psi - Model 006024-2 (49-State & Canada)
UPC: 696471060279

Model 006025-0 (50-State)
UPC: 696471060256



FEATURES

GENERAC OHV ENGINE

- Low Oil Shutdown on all Models

EASY ACCESS

- Axial cam pump is well above the ground, making hose connections easy.
- Engine Controls (clearly marked for easy starting)

MOBILITY

- Balanced for almost effortless mobility, regardless of terrain.
- Pump height makes it easy to gather hoses for transport.

COMFORT

- Cushion Grip (provides greater comfort while cleaning)
- Easy-to-pull trigger reduces fatigue.
- Longer gun – improved grip surface.
- Rear hose connection on spray gun provides better balance and comfort.

COMPACT DESIGN

- Doesn't take up much room in the garage or shed

2500 • 2700 • 3100 psi

specifications

PRESSURE AND FLOW

Outlet Pressure (psi/bar)	2500/172 - 006020-3 2700/186 - 006022-3 & 006023-0 3100/213 - 006024-2 & 006025-0
Flow Rate (gpm)/(L/min)	2.3/8.7 - 2500 & 2700 psi 2.7/10.2 - 3100 psi

ENGINE

Manufacturer	Generac
Displacement (in³/cc)	11.9/196 - 2500 & 2700 psi 12.9/212 - 3100 psi
Type	OHV (Overhead Valve)
Orientation	Horizontal
Low Oil Shutdown System	Yes
Fuel Capacity (qt/L)	0.8/3
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	SAE 30 or 10W30
Throttle Control	Manual
Choke	Manual
Starting Method	Manual

PUMP

Type	Axial cam
Plunger	Stainless steel
Material	Aluminum body & head - 2500 & 2700 psi Aluminum body, brass head - 3100 psi
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	25/7.6 - 2500 & 2700 psi 30/9.1 - 3100 psi
Diameter (in/mm)	.25/6.4
Rating (psi/bar)	3100/213
Connectors	M22 threaded

DETERGENT SYSTEM

Number of Chemical Tanks per Unit	0 - 2500 psi 1 - 2700 psi 2 - 3100 psi
Chemical Tank Description	Siphon hose - 2500 psi 3/4 gallon (2.8 liters) - 2700 & 3100 psi

NOZZLES

Number of Nozzles per Unit	3 - 2500 psi 4 - 2700 psi 5 - 3100 psi
Nozzle Descriptions	0, 25, soap - 2500 psi 0, 25, 40, soap - 2700 psi 0, 15, 25, 40, soap - 3100 psi

GUN & LANCE

Gun	Standard - 2500 & 2700 psi Deluxe - 3100 psi
Gun to Lance Connection	M22 threaded
Gun to Hose Connection	M22 threaded
Lance Length (in/cm)	20/51
Lance to Nozzle Connection	Quick change
Lance Material	Chrome-plated steel
Lance Connector Material	Brass

FRAME & MISC.

Handle	Fixed
Frame Construction	Welded steel
Wheels (in/cm)	1.5 x 10/3.8 x 25.4 never flat

DIMENSIONS & WEIGHTS

Length (in/cm)	23.25/59.1
Width (wheel to wheel, in/cm)	16/40.6
Height (in/cm)	40.25/102.2
Weight Including Hose, Gun & Lance (lbs/kg)	60.3/27.4 - 2500 psi 61.5/27.9 - 2700 psi 67.5/30.6 - 3100 psi
Boxed Weight (lb/kg)	68/30.8 - 2500 psi 69/31.3 - 2700 psi 74/33.6 - 3100 psi
Boxed Length (in/cm)	27.5/69.9
Boxed Width (in/cm)	18/45.7
Boxed Height (in/cm)	22/55.9

WARRANTY

Warranty	2 year limited
----------	----------------