

Part Number: C1804

Revision Level: 11/19/2012

2C 16 AWG (65/34) OFHC BC PP, PVC**COMMAND® SERIES****A. CONSTRUCTION**

Conductor:	16 AWG 65/34 BC	.059" nom
Insulation:	.009" Wall, Polypropylene (PP)	.077" nom
Cable Core:	2C @ 6.00" LHL	.154" nom
Jacket:	.030" Polyvinyl Chloride (PVC)	.214" nom
Print Legend:	CAROL ® -- C1804 -- COMMAND OFHC HD 16AWG 2C ROHS -- 75C E60233-8 (UL) CL3 -- LL69381 CSA AWM I/II A/B 80C 600V FT4 -- (Date code) (Seq Footage)	

DIAMETERS**B. INDUSTRY APPROVALS**

National Electrical Code	Article 725
UL Standard 444	Type CL3
CSA International	Type AWM I/II A/B

C. ELECTRICAL PROPERTIES

Temperature:	-20°C to +80°C
Suggested Working Voltage:	600V Max
Conductor DCR:	4.21 Ohms/M' @ 20°C (nom)
Mutual Capacitance:	22.1pF/ft @ 1kHz (nom)

D. COLOR CODE

Item	COLOR
1	BLACK
2	RED

E. CUSTOMER APPROVAL

Signature: _____
Date: _____