

Part Number: C2040A

Revision Date:

1/9/2013

1C 20 AWG 10/30 TC PVC**HOOK UP WIRE****A. CONSTRUCTION**

Conductor: #20 AWG 10/30 Tinned Copper

Insulation: .016" Polyvinyl Chloride (PVC)

Print Legend:

CAROL A 20 AWG RU AWM 80C VW-1 E18621-8 --- CSA LL69381 FT-1 TR64 90C --- ***DIAMETERS**

.038" Nom

.070" Nom

Note *

NOTE: THIS PRODUCT IS ONLY MARKED 80C AS PER UL STYLE 1007, HOWEVER, IT ALSO MEETS 105C AS PER UL STYLE 1569

B. INDUSTRY APPROVALS

UL Standard 758

AWM Style 1007 / 1569

CSA International

Type TR64

C. ELECTRICAL PROPERTIES

Temperature:

-20°C to +105°C

Suggested Working Voltage:

300V Max

Conductor DCR:

10.9 Ohms/M' @ 20°C (Max)

D. CUSTOMER APPROVAL

Signature: _____

Date: _____