

Name	Socket Weld Flange
Product Code	S1034SW4006N
Product Name	3/4" 304/L Stainless Steel Forged 300# ANSI RF Socket Weld Flange Sch 40
Family Code	S1034SW4
Alloy	304\304L Stainless Steel
Bore Schedule	Sch 40
Pressure Rating	300#
Size	3/4"
Outside Diameter	4.62"
Thickness	0.62"
Bore	1.09"
Length Through Hub	1.00"
Hub	
Depth of Socket	0.44"
Hub Diameter	1.88"
Bolt Circle	3.25"
Bolt Hole Size	0.75"
Holes Diameter	0.75"
Number Of Bolt Holes	4
Materials	Forged Stainless Steel
Weight	2.6455
Standards	ASME A182 (Forging), ASME B16.5 (Dimensions), ASME B1.20.1 (Threads)

