



I. Product Description

Green Force® Glass & Surface Cleaner is ideally suited to clean soiled glass and other hard surfaces. It effectively cuts greasy films and soils, leaving surfaces sparkling clean. **Green Force® Glass & Surface Cleaner** is versatile and safe enough to use on your most delicate glass surfaces, yet is strong enough to quickly cut through the toughest dirt, dust, fingerprint and haze deposits.

NOTE: Green Force® Glass & Surface Cleaner is ready to use (RTU) in the 32 fl. oz. package and is water dilutable in the 1 gallon package.

II. Applications

Green Force® Glass & Surface Cleaner is perfect for Glass, Fiberglass, Mirrors, Stainless Steel, Countertops, Porcelain Tile, Windowsills, Plastic and Vinyl Surfaces and much more without the ammonia odor.

III. Features & Benefits

- **Environmentally preferred product.** U.S. EPA Design for Environment (DfE) recognized.
- **Biodegradable**
- **Low VOC Content.** Reduces contributions to ground smog by volatile organic compounds.
- **Professional Strength.** Formulated for the toughest glass and surface applications.
- **Non Ammoniated.** Effective cleaner without harsh odor.
- **Non-Abrasive.** Will not scratch or score equipment finish.
- **Non-Flammable.** Aqueous formulation reduces risk of fire (see MSDS for details).

IV. Physical Properties

Flash Point	None		Boiling Point	212° F	
Odor	<u>RTU</u> Bland	<u>Bulk</u> Floral	Freezing Point	32° F	
Appearance	<u>RTU</u> Clear Liquid	<u>Bulk</u> Blue Liquid	Solubility	Soluble in H ₂ O	
Vapor Density	Not Determined		% Solids	Not Determined	
VOC Content (Fed)	<u>RTU</u> <9.3 g/L	<u>Bulk</u> <10.1 g/L	VOC %	<u>RTU</u> <1%	<u>Bulk</u> <1%
Sara Title III, Sect. 313 Chemicals	None		Specific Gravity	<u>RTU</u> 0.993	<u>Bulk</u> 0.996
Prop 65	No		pH	7.2-8.5	

V. Specifications and Approvals

- Recognized by the U.S. Environmental Protection Agency Design for the Environment (DfE) Formulator Initiative.

VI. Directions

- The 32 fl. oz. SKU (14460) is ready to use. No shaking or dilution is necessary.
- For the one gallon SKU (14461), dilute with water 1 to 20 (6 oz. per gallon).
- Spray solution onto surface.
- Wipe clean and polish dry with a clean, dry lint-free cloth.
- For very dirty glass surfaces, allow Green Force™ Glass & Surface Cleaner to penetrate the soil for 30 to 60 seconds.
- For use as an all-purpose cleaner, use no more than two pints of concentrate with water to make one gallon (1 to 3).

VII. Package Description

Part Number	Container Size
14460	32 oz Spray Bottle
14461	1 Gallon Bottle

VIII. Disposal

Disposal requirements vary by state and local jurisdiction. All used and unused product should be disposed of in conformance with local, state and federal regulations.

IX. Special Use Warnings

General

Use only in well ventilated area. Ventilation may be improved by opening a window or door or providing mechanical assistance. Avoid continuous breathing of vapor and spray mist. Avoid contact with skin and eyes. For more information regarding short-term and long-term exposure, review the Material Safety Data Sheet for this product.

DISCLAIMER: This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. All products should be tested for suitability on a particular application prior to actual use. CRC Industries, Inc. makes no representations or warranties of any kind concerning this data.

CRC Industries, Inc.
Technical Service: (800)521-3168

Industrial Products Division
Customer Service: (800)272-4620

Warminster, PA 18974
CRC On-Line: (215)442-6260