

DEWALT®

20V MAX*
LITHIUM ION

HEATED JACKETS

12V MAX*
LITHIUM ION

20V/12V MAX* LITHIUM ION SOFT SHELL WORK JACKET



DURABLE WATER AND WIND RESISTANT OUTER SHELL



LED CONTROLLER WITH 3 TEMPERATURE SETTINGS AND PRE-HEAT MODE



DEWALT 20V MAX* AND 12V MAX* BATTERIES CAN PROVIDE HOURS OF CORE BODY WARMTH AND CONTINUOUS HEAT**



USB CHARGING CAPABILITY FOR 2 ELECTRONIC DEVICES



USB POWER SOURCE FUEL GAUGE INDICATES STATE OF CHARGE FOR BATTERIES



HOODED



CAMO



BLAZE



GUARANTEED TOUGH.®

Copyright © 2013 DeWALT. The following are trademarks for one or more DeWALT power tools and accessories. The yellow and black color scheme, the "D" shaped air intake grille, the array pyramids on the handgrip, the kit box configuration, and the array of lozenge-shaped humps on the surface of the tool.

With respect to 20V MAX, maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

**With respect to 12V MAX*, maximum initial battery voltage (measured without a workload) is 12 volts. Nominal voltage is 10.8.

**Actual run time varies depending on battery type and heat setting.

The TRUE TIMBER registered trademark and the DS1 and Snowfall Blaze camo design are owned by True Timber Outdoors Holding Company, LLC.

ICDWHTJKTCC