

DEWALT®

HEATED JACKETS

DEWALT®

Powered by 20V MAX* or 12V MAX* batteries, DEWALT'S HEATED JACKETS provide hours of warmth and comfort when the temperature dips.

Constructed from heavy-duty materials, these jackets stand up to tough jobsite conditions and are stylish enough to wear around town. Each jacket comes with a fuel gauge equipped battery power adaptor and USB power ports.



USB POWER SOURCE IS COMPATIBLE WITH ALL DEWALT 20V MAX* OR 12V MAX* BATTERIES



UP TO 4-CORE HEATING ZONES



DURABLE WATER AND WIND RESISTANT OUTER SHELL



LED CONTROLLER WITH 3 TEMPERATURE SETTINGS AND PRE-HEAT MODE



USB CHARGING CAPABILITY FOR 2 ELECTRONIC DEVICES



DEWALT 20V MAX* AND 12V MAX* BATTERIES CAN PROVIDE HOURS OF CORE BODY WARMTH AND CONTINUOUS HEAT**



USB POWER SOURCE FUEL GAUGE INDICATES STATE OF CHARGE FOR BATTERIES

1 YEAR LIMITED WARRANTY

1 YEAR FREE SERVICE

90 DAY MONEY BACK GUARANTEE

1-800-4 DEWALT®
WWW.DEWALT.COM



HEATED JACKETS

GUARANTEED TOUGH.®

With respect to 20V MAX, maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.
**Actual run time varies depending on battery type and heat setting

Copyright © 2013 DEWALT. The yellow/black color scheme is a trademark for DEWALT power tools & accessories. Product may differ from that pictured. Does not affect function.

20V MAX*
LITHIUM ION

12V MAX*
LITHIUM ION

DCHJ060 Soft Shell Work Jacket

| | |
|----------------------|---|
| Voltage | 20V MAX* & 12V MAX* |
| Heat Zones | 4 (Left / Right Chest, Mid-Back and Collar) |
| Heat Settings | High, Medium, Low + Pre-Heat |
| Color | Black |
| Pockets | 5 |



DCHJ060C1 Includes: DCB201 20V MAX* Lithium-Ion Battery (1.5 Ah), Fast Charger and DCB091 USB Power Source
DCHJ060B Includes: DCB091 USB Power Source

DCHJ061 Hooded Work Jacket

| | |
|----------------------|-------------------------------------|
| Voltage | 20V MAX* & 12V MAX* |
| Heat Zones | 3 (Left / Right Chest and Mid-Back) |
| Heat Settings | High, Medium, Low + Pre-Heat |
| Color | Black |
| Pockets | 4 |



DCHJ061C1 Includes: DCB201 20V MAX* Lithium-Ion Battery (1.5 Ah), Fast Charger and DCB091 USB Power Source
DCHJ061B Includes: DCB091 USB Power Source

DCHJ062 TRUE TIMBER® Camo Jacket

| | |
|----------------------|---|
| Voltage | 20V MAX* & 12V MAX* |
| Heat Zones | 4 (Left / Right Chest, Mid-Back and Collar) |
| Heat Settings | High, Medium, Low + Pre-Heat |
| Color | TRUE TIMBER® DS1 Camo |
| Pockets | 7 |



DCHJ062C1 Includes: DCB201 20V MAX* Lithium-Ion Battery (1.5 Ah), Fast Charger and DCB091 USB Power Source
DCHJ062B Includes: DCB091 USB Power Source

DCHJ063 TRUE TIMBER® Blaze Camo Jacket

| | |
|----------------------|---|
| Voltage | 20V MAX* & 12V MAX* |
| Heat Zones | 4 (Left / Right Chest, Mid-Back and Collar) |
| Heat Settings | High, Medium, Low + Pre-Heat |
| Color | TRUE TIMBER® Blaze Camo |
| Pockets | 7 |



DCHJ063C1 Includes: DCB201 20V MAX* Lithium-Ion Battery (1.5 Ah), Fast Charger and DCB091 USB Power Source
DCHJ063B Includes: DCB091 USB Power Source

DCHJ060 Soft Shell Work Jacket



DCHJ061 Hooded Work Jacket



DCHJ062 TRUE TIMBER® Camo Heated Jacket



DCHJ063 TRUE TIMBER® Blaze Camo Heated Jacket



HEATED JACKETS