

MICRO SWITCH™ 914CE Miniature Limit Switch

Product Nomenclature



For example, a **914CE29-3** part number would define a 914CE Series miniature limit switch with a panel mount perpendicular top roller plunger and three feet of cable.



914CE
↓
Switch Type

914CE Series
Small Precision
Limit Switch

29
↓
Actuator Type

1 Top pin plunger	27 Top pin plunger panel mount
2 Top roller plunger, parallel	28 Top roller plunger, parallel panel mount
3 Top roller plunger, perp.	29 Top roller plunger, perp. panel mount
16 Front rotary	31 Top roller plunger, parallel boot seal
18 Top pin plunger w/ boot seal	55 Top roller plunger, perp. boot seal
19 Top adjustable pin plunger	66 Top ball bearing plunger
20 Coil wobble	
22 Manually oper. nylon button	

3
↓
Cable Length

3 3 feet
6 6 feet
9 9 feet
12 12 feet
15 15 feet

↓
Options

A Side entry
G Gold contacts
P Top mounting
L1 Low temp. -40 °C, cable not for flexing
V Vitron seals/gasket (front rotary only)

Bottom exit is standard.

↓
Connectors

Q dc type Brad Harrison
Q1 ac type two keyways
Q2 dc type plastic

NOTE: not all combinations of model code are available.
Please contact your Honeywell provider/representative for assistance.