

### DIMENSIONAL SPECIFICATIONS

---

#### **Overall Dimensions:**

Nominal Dimension: 36" x 20" x 29-1/2" (W-D- H)

Actual Dimension: 36-1/16" x 19-7/8" x 29-7/8" (W-D- H)

#### **Knee Space Between Pedestals:**

N/A

#### **Inside Storage Space:**

Two Compartments:

33-23/32" x 12-11/16" x 12-9/16" (W-D-H)

### MATERIAL SPECIFICATIONS

---

#### **Top:**

- 1-1/8" thick particleboard with Kraft backer bottom and high-pressure laminate (HPL) top cover.
- Top dimensions—36-1/16" x 19-7/8"(W-D)

#### **End Panels:**

- 1-1/8" thick particleboard with melamine surface back, and high-pressure laminate (HPL) surface top cover and .8 mm edge trim on the bottom.
- End panel dimensions –19-27/32"x 28-1/8" (W-H)

#### **Back:**

- 3/4" particleboard with melamine both front and back, and .5 mm edgebanding on side.
- Back dimensions-33-23/32"x 27-31/32" (W-H)

#### **Shelf:**

- 3/4" particleboard with melamine both front and back
- Bottom Shelf Dimensions –33-23/32" x 18-13/64" (W-D)
- Adjustable Shelf Dimensions- 33-45/64" x 12-45/64" (W-D)  
-Adjusts in 1-1/4" increments with a total range of 6-1/4"

#### **Doors:**

- 3/4"particleboard core, impact resistant thermally fused laminate decorative cover.
- Door Dimensions-16-46/64" x 3 /4" x 25-7/64"(W-D-H)



# 10700 Series H107291 Technical Specifications

## Hardware:

Hardware Pack-251-1506

Product Pack-262-7740

Shelf Pack-262-3546

## MODEL FEATURES

---

- .625 Radius edge on 107 tops
- **Lock #**-50-5577
- **10700** Series wood produce meets or exceeds **ISTA** shipping and **ANSI/BIFMA X5.5** (latest Rev.) testing requirements for office furniture.
- \*\*\*Classical contemporary styling, and hardwood accents.

**PARTICLEBOARD: All particleboard is ANSI grade IM3 or better.**

## CARTONING INFORMATION

---

**Carton-Outside Dimensions:** 38-3/32" x 22-3/32" x 31-27/32"

**Cubes:** 15

**Carton #:** 242-7610

**Weight:** 147 lbs